



Main

Range	Spacial
Product name	Spacial S3DEX
Device application	ATEX certified application
Product or component type	Compact enclosure
Enclosure nominal height	500 Mm
Enclosure nominal width	400 Mm
Enclosure nominal depth	200 Mm
Door type	Plain
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Installation accessory type	Wall-mounting
Product destination	For potentially explosive atmosphere
Device composition	1 door 1 lock body with clamped blind nut

Complementary

Variant particularity	Single piece body Gutter-shaped front rail double sheet thickness
Number of doors	Front face: 1 door(s)
Door opening side	Reversible (120 °)
Lock type	Double-bar lock
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Steel
Surface finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)
Standards	EN 60079-0:2012 EN 60079-7:2007 EN 60079-31:2009
Marking	II 2 GD Ex e IIC Gb Ex tb IIIC Db according to the ATEX directive 94/9/EC
Net weight	9.5 Kg

Environment

IP degree of protection	IP66 conforming to IEC 60529 (enclosures with single door)
IK degree of protection	IK10 conforming to IEC 62262

Packing Units

Package 1 Weight	9.5 Kg
------------------	--------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**