

A.C. INPUT FUSING

Model	Fuse 100/120VAC	Fuse 220/240VAC	Model	Fuse 100/120VAC	Fuse 220/240VAC
HA5-1.5/OVP-A.....	0.25A.....	0.125A	HN5-9/OVP-A.....	2A.....	1A
HA15-0.9-A.....	0.25A.....	0.125A	HN12-5.1-A.....	2A.....	1A
HA24-0.5-A.....	0.5A.....	0.25A	HN15-4.5-A.....	2A.....	1A
HAA5-1.5/OVP-A.....	0.5A.....	0.25A	HN24-3.6-A.....	2A.....	1A
HAA15-0.8-A.....	0.75A.....	0.375A	HN28-3-A.....	2A.....	1A
HAA24-0.6-A.....	0.75A.....	0.375A	HD5-12/OVP-A.....	2A.....	1A
HAA512-A.....	0.75A.....	0.375A	HD12-6.8-A.....	2A.....	1A
HAD12-0.4-A.....	0.5A.....	0.25A	HD15-6-A.....	2A.....	1A
HAD15-0.4-A.....	0.5A.....	0.25A	HD24-4.8-A.....	2.5A.....	1A
HTAA-16W-A.....	0.75A.....	0.375A	HD28-4-A.....	2A.....	1A
HB5-3/OVP-A.....	0.5A.....	0.25A	HD48-3-A.....	3A.....	1.5A
HB12-1.7-A.....	0.5A.....	0.25A	HDD15-5-A.....	3A.....	1.5A
HB15-1.5-A.....	0.5A.....	0.25A	HDBB-105W-A.....	3A.....	1.5A
HB24-1.2-A.....	0.75A.....	0.375A	HDCC-150W-A.....	4A.....	2A
HB28-1-A.....	0.75A.....	0.375A	HE5-18/OVP-A.....	3A.....	1.5A
HB48-0.5-A.....	0.75A.....	0.375A	HE12-10.2-A.....	3A.....	1.5A
HB120-0.2-A.....	0.75A.....	0.375A	HE15-9-A.....	3A.....	1.5A
HB200-0.12-A.....	0.75A.....	0.375A	HE24-7.2-A.....	4A.....	2A
HB250-0.1-A.....	0.75A.....	0.375A	HE28-6-A.....	3A.....	1.5A
HBB5-3/OVP-A.....	1A.....	0.5A	HE48-4-A.....	4A.....	2A
HBB15-1.5-A.....	1A.....	0.5A	F5-25/OVP-A.....	3A.....	1.5A
HBB24-1.2-A.....	1.5A.....	0.75A	F15-15-A.....	6A.....	3A
HBB512-A.....	1A.....	0.5A	F24-12-A.....	6A.....	3A
HBAA-40W-A.....	1.5A.....	0.75A	G5-35/OVP-A.....	4A.....	2A
HC5-6/OVP-A.....	1A.....	0.5A	CP131-A.....	3A.....	1.5A
HC12-3.4-A.....	1A.....	0.5A	CP162-A.....	3A.....	1.5A
HC15-3-A.....	1A.....	0.5A	CP197-A.....	6.5A.....	3.25A
HC24-2.4-A.....	1.5A.....	0.75A	CP205-A.....	1A.....	0.5A
HC28-2-A.....	1A.....	0.5A	CP323-A.....	2A.....	1A
HC48-1-A.....	1A.....	0.5A	CP379-A.....	3A.....	1.5A
HCC5-6/OVP-A.....	2A.....	1A	CP498-A.....	2.5A.....	1.5A
HCC15-3-A.....	2A.....	1A	CP503-A.....	3A.....	1.5A
HCC24-2.4-A.....	3A.....	1.5A	CP510-A.....	3A.....	1.5A
HCC512-A.....	3A.....	1.5A			
HCAA-60W-A.....	2A.....	1A			
HCBB-75W-A.....	2A.....	1A			

Notes:

WARNING! RISK OF FIRE! EXTERNAL LINE FUSE MUST BE USED!

Usage in North American Countries, Fuse Type: 3AG (1/4 x 1 1/4 inch), Slow Blow, 250V, must be UL Listed and CSA Certified to maintain safety approvals.

Usage in European Countries, Fuse Type: 5 x 20mm, Time-lag, 250V, must be IEC Pub. 127 approved to maintain safety approvals.