

REG24PTP1RHU

temperature control relay REG - 24 x 48 mm -
100..240 V AC - 1 relay C/O



Main

Range of product	Zelio Control
Product or component type	Modular measurement and control relays
Relay type	Temperature control relays
Product specific application	Heating or cooling HVAC Industrial machines Packaging
Relay name	REG
Outer dimension	1/32 DIN 24 x 48 mm
Analogue input type	Temperature probe Pt 100 Thermocouple thermocouple J, K, R, B, S, T, E, N, PLII
[Us] rated supply voltage	100...240 V
Output type	1 relay C/O at 220 V AC / 3 A
Communication port protocol	Modbus

Complementary

Supply voltage limits	85...264 V
Measurement accuracy	0.5 % full scale
Sampling duration	500 ms
Power consumption in VA	6 VA at 100 V AC 8 VA at 240 V AC
Method of access	Slave
Transmission frame	RTU
Physical interface	RS485 non isolated
Exchange mode	Half duplex
Transmission rate	9600, 19200 kbit/s
Function available	Auto tuning Fuzzy logic Hysteresis on-off PID Ramp 8 steps
Marking	CE
Operating position	Any position
Local signalling	1 LED for Modbus alarm (AL2) 1 LED green for setpoint value indicator (SV) 1 LED red for process output 1 active (C1) 4 digits 7 segments red for process value
Mounting support	35 mm symmetrical DIN rail Panel


The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company Schneider Electric. This information is not intended to be used as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	CSA C22-2 No 24-93 EN 61010-1 EN 61326-1
Product certifications	CURus (873) GOST
Ambient air temperature for storage	-20...60 °C
Ambient air temperature for operation	-10...50 °C
Relative humidity	90 % without condensation
Operating altitude	2000 m
Storage altitude	3000 m
Vibration resistance	1 gn at 10...70 Hz conforming to IEC 60068-2-6
Shock resistance	5 gn conforming to IEC 60068-2-27
IP degree of protection	IP20 (rear) IP66 (front face) conforming to IEC 60529
NEMA degree of protection	NEMA 4X (front face)


24 x 48 Size – 1/32 DIN Standard

Panel Mounting: Bracket Supplied




- (1) Seal
(2) Fixing brackets supplied with REG temperature control relays.

Panel cut-out




- (3) Minimum value.

Side stick mounting: n units (water-proof property lost in this case)



Mounting on DIN Rail with Accessory REG24PSOC



Temperature Control Relays

Wiring Diagram

