

Product data sheet

Specifications



STD - DIN - remote control dimmer - 1000 W

CCTDD20003

Main

range of product	Acti9
Product name	Acti9 STD
Product or component type	Remote control dimmer
Device short name	STD

Complementary

Device application	Building
Load type	230 V AC halogen lamp: 60...1000 W 230 V AC incandescent lamp: 60...1000 W low voltage halogen lamp with conventional transformer: 60...1000 W motor: 60...600 W
Control type	Local control: push-button Remote control: push-button
Power consumption in VA	0.8 VA
Thermal losses	3 W
Input type	Push-button
[Ue] rated operational voltage	230 V AC +/- 10 % at 50 Hz
Protection type	Electronic over temperature protection Electronic overvoltage protection Single shot thermal fuse Electronic overload protection
Mounting support	DIN rail
9 mm pitches	8
Connected auxiliaries	Maximum 25 auxiliary push-buttons without light indication, distance : < 50 m Maximum 5 auxiliary push-buttons with light indication, distance : < 50 m
Connections - terminals	Screw terminals, 2 cable(s) 4 mm² top
Height	85 mm
Width	72 mm
Depth	62 mm
Product weight	120 g

Environment

IP degree of protection	IP20
Standards	EN 60669-2-1
Directives	73/23/EEC - low voltage directive 89/336/EEC - electromagnetic compatibility

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient air temperature for operation	0...70 °C
Ambient air temperature for storage	0...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.000 cm
Package 1 Width	9.500 cm
Package 1 Length	9.500 cm
Package 1 Weight	183.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	24
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.228 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	679a8b51-f3fb-4380-a88d-59b4cb86573e
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer

Lifetime extension	
Repair	No

Use Again

Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins