

M18 CAG115XPDB-502X | M18 FUEL™ 115 mm braking grinder

Article: 4933451010



- Milwaukee® designed and built brushless POWERSTATE™ motor with the power to grind and up to 10x more tool life.
- FIXTEC nut for tool-free disc change.
- Anti-vibration side handle for lower vibration.
- Individual battery cell monitoring optimises tool run time and ensures long term pack durability.
- Fuel gauge displays remaining charge.
- Flexible battery system: works with all Milwaukee® M18™ batteries.
- REDLINK PLUS™ intelligence system delivers an advanced digital overload protection for tool and battery and uniquely enhances the tool performance under load.

M18 CAG115XPDB-502X	
Sound pressure level (dB(A))	78.9
Sound pressure level uncertainty (dB(A))	3
Sound power level measured (dB(A))	89.9
Sound power level measured uncertainty (dB(A))	3
Vibration grinding (m/s ²)	2.11
Vibration grinding uncertainty (m/s ²)	1.5
Vibration sanding (m/s ²)	1.83
Vibration sanding uncertainty (m/s ²)	1.5
No load speed (rpm)	8500
Voltage (V)	18
Battery pack capacity (Ah)	5.0
Battery type	Li-ion
Braking time (s)	< 2
Supplied in	HD Box
Charger supplied	59 min
No. of batteries supplied	2
Spindle size	M 14
Article Number	4933451010
Weight with battery pack (kg)	2.7
Switch type	Paddle switch
Max. cutting depth (mm)	28
Line lock out function	Yes
Disc diameter (mm)	115