

Technical data


6411

Single row deep groove ball bearings



Deep groove ball bearing, radial contact, pressed steel cage, open

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	55 mm
D - External diameter	140 mm
B - Bearing/Inner ring width	33 mm
rs - Min fillet radius	2,1 mm
Radial clearance class	CN
Mass	2,29 kg

PRODUCT PERFORMANCE

C - Dynamic load	98500000 mN
C0 - Static load	54000000 mN
Cu - Fatigue limit load	4200000 mN
f0 - Coefficient	12.7
N lim - Oil lubrication limit speed	36600 °/s
N lim - Grease lubrication limit speed	31200 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	66 mm
Da max - Max shoulder diameter OR	129 mm
ra max - Max shaft & housing fillet radius	2 mm



INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.F_r + Y.F_a$

$\frac{f_0 F_a}{C_0}$	e	Fa / Fr ≤ e		Fa / Fr > e	
		X	Y	X	Y
0.172	0.19	1	0	0.56	2.3
0.345	0.22				1.99
0.689	0.26				1.71
1.03	0.28				1.55
1.38	0.3				1.45
2.07	0.34				1.31
3.45	0.38				1.15
5.17	0.42				1.04
6.89	0.44				1

Equivalent static radial load

$P_0 = X_0.F_r + Y_0.F_a$

X_0	Y_0
0.6	0.5

For single or DT bearing arrangement :

If $P_0 < F_r$, then use $P_0 = F_r$

