



Product data sheet

Power tools for trade & industry

Random Orbit Sander

PRO GEX 125



Comfortable sanding for getting more done

The most important data

Rated input power	290 W
Sanding pad diameter	125 mm
Orbit diameter	2.6 mm

Part Number 0 601 3A8 070

Technical data

Technical data

Sanding pad diameter	125 mm
No-load speed	7,500 – 12,000 rpm
Orbital stroke rate	15,000 – 24,000 opm
Eccentricity	1.3 mm
Rated input power	290 W
Weight	1.4 kg
Orbit diameter	2.6 mm
Packaging dimensions (width x length x height)	136 x 216 x 167 mm

Noise/vibration information

Sanding solid wood

Vibration emission value ah	3.8 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Superior random orbital sander for comfortable, highly efficient sanding
- Less hand fatigue and numbness ensured by low tool vibration of 3.8 m/s²
- Effortless sander control and guidance thanks to well-balanced design
- High material removal rate with 290-watt motor power
- Optimal for sanding wood, paint, plaster, and metal surfaces



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

