


647000-9  OBSOLETE

TE Internal #: 647000-9

TE Internal Description: 09P MTA100 PSTD CONN ASSY SN

MTA Plug: Nylon, Tin Plated, 2.54 mm, with Mating Alignment

[View on TE.com >](#)



All MTA Plug: Nylon, Tin Plated, 2.54 mm, with Mating Alignment (28)

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #52955-1
TERMINAL,PG SPR SPD 16-14 6




TE Part #61794-1
RING 18-14 AWG TPST



TE Part #3-520402-2
ULTRA-FAST 187 ASY REC 16-14 AWG
TPBR



TE Part #3-520406-2
ULTRA-FAST 250 ASY REC 16-14 AWG
TPBR



TE Part #3-521057-2
ULTRAFAST 250 ASSY TAB 16-14
AWG TPBR



TE Part #CAT-104MTA-NYLCC
Nylon PCB Connector Covers: 2.54 mm,
mm, MTA 100



TE Part #CAT-104MTA-NTPMR
Nylon Tin Plated Receptacle: 2.54 mm,
with Mating Alignment, MTA 100

Documents

Product Drawings

[09P MTA100 PSTD CONN ASSY SN](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_647000-9_F.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_647000-9_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_647000-9_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Agency Approvals

Agency Approval Document

English

647000-9

09P MTA100 PSTD CONN ASSY SN

