

LC1N0610B5N

Contactor, Easy TeSys

Control, LC1N, 3P(3NO), AC-3, ≤440V, 6A, 24V

AC coil, 50Hz, 1NO auxiliary contact, China



Main

Range	Easy TeSys
Range of product	Easy TeSys Control
Product or component type	Contactor
Device short name	LC1N
Contactor application	Resistive load Motor control
Utilisation category	AC-3 AC-1 AC-4
Poles description	3P
[Ue] rated operational voltage	Power circuit: ≤ 690 V AC 50/60 Hz
[Ie] rated operational current	6 A (at <60 °C) at ≤ 440 V AC AC-3 for power circuit 20 A (at <60 °C) at ≤ 440 V AC AC-1 for power circuit 3.1 A (at <60 °C) at ≤ 440 V AC AC-4 for power circuit
[Uc] control circuit voltage	24 V AC 50 Hz

Complementary

Motor power kW	1.5 kW at 220...230 V AC 50/60 Hz 2.2 kW at 380...400 V AC 50/60 Hz 2.2 kW at 415...440 V AC 50/60 Hz 3 kW at 500 V AC 50/60 Hz 3 kW at 660...690 V AC 50/60 Hz
Pole contact composition	3 NO
[Ith] conventional free air thermal current	20 A (at 60 °C) for power circuit
Irms rated making capacity	60 A at 380 V AC for power circuit conforming to IEC 60947-4-1 140 A AC for auxiliary contact conforming to IEC 60947-5-1
Rated breaking capacity	48 A at 440 V for power circuit conforming to IEC 60947
[Icw] rated short-time withstand current	80 A 40 °C - 10 s for power circuit 45 A 40 °C - 60 s for power circuit 20 A 40 °C - 600 s for power circuit
Associated fuse rating	10 A gG at ≤ 690 V coordination type 1 for control circuit conforming to IEC 60947-5-1 12 A gG at ≤ 690 V coordination type 1 for power circuit
Average impedance	2.5 mOhm - Ith 20 A 50 Hz for power circuit
Power dissipation per pole	0.09 W AC-3 1 W AC-1
[Ui] rated insulation voltage	690 V conforming to IEC 60947-4-1
Overvoltage category	III
Pollution degree	3
[Uimp] rated impulse withstand voltage	6 kV coil not connected to the power circuit conforming to IEC 60947
Mechanical durability	10000000 cycles
Electrical durability	1400000 Cycles AC-3 150000 Cycles AC-1 250000 cycles AC-4
Control circuit type	AC at 50 Hz

Control circuit voltage limits	0.85...1.1 U _c (-5...55 °C):operational 50 Hz 0.3...0.6 U _c (-5...55 °C):drop-out 50 Hz
Inrush power in VA	95 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-in power consumption in VA	8.5 VA 50 Hz cos phi 0.3 (at 20 °C)
Heat dissipation	2...3 W for control circuit
Operating time	12...22 ms on closing 4...19 ms on opening
Maximum operating rate	1800 cyc/h 60 °C
Connections - terminals	Power circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 1...2.5 mm ² - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 1...4 mm ² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 1...4 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 2 1...2.5 mm ² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 1...4 mm ² - cable stiffness: solid without cable end
Tightening torque	Power circuit: 1.2 N.m Control circuit: 1.2 N.m
Auxiliary contact composition	1 NO
Minimum switching voltage	17 V for control circuit
Minimum switching current	5 mA for control circuit
Insulation resistance	> 10 MOhm for control circuit
Non-overlap time	1.5 Ms on energisation guaranteed between NC and NO contact 1.5 ms on de-energisation guaranteed between NC and NO contact
Mounting support	DIN rail Plate

Environment

Standards	GB 14048.4 IEC 60947-1 EN 60947-4-1 IEC 60947-4-1 EN 60947-1
Product certifications	CCC
IP degree of protection	IP20 conforming to IEC 60529
Protective treatment	TH (pollution degree 3) conforming to IEC 60068
Permissible ambient air temperature around the device	-5...55 °C operation -60...80 °C storage -20...70 °C at U _c
Operating altitude	3000 m without derating
Fire resistance	850 °C conforming to IEC 60695-2-1
Mechanical robustness	Vibrations contactor open (1.5 Gn, 5...300 Hz) Vibrations contactor closed (3 Gn, 5...300 Hz) Shocks contactor open (7 Gn for 11 ms) Shocks contactor closed (10 Gn for 11 ms)
Height	74 mm
Width	45 mm
Depth	80 mm
Net weight	0.3 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.87 cm
Package 1 Width	7.42 cm
Package 1 Length	8.39 cm
Package 1 Weight	349.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	36
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	13.0 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	576
Package 3 Height	60.0 cm
Package 3 Width	80.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	201.074 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins