



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2019 (201) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #HC5956
BATT.LEAD 90 DEG 70MM+VE.



TE Part #CAR2PC68-001
CAR PLUG DIN9680 2way, IP68



TE Part #K1128688
Battery Disconnecter 35-411-130-R-900



TE Part #DARS24296-000A3
CAR PIN STANDARD CONT. #5, silver plated





TE Part #SRK-PC-080-35-601
PIN, SOLID, SIZE M8, 35mm2, AG



TE Part #DTSK06-1-08SB
PLUG, INLINE, KEY B



TE Part #K1012918
Relay 26-70-04



TE Part #HC5957
BATT.LEAD 90 DEG 70MM-VE.



TE Part #DT06-2S-P060
PLG, 2P, BLK, BUSBAR 1X2, NICKEL



TE Part #K1127684
Relay 29-112-12

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_1452656-2_C.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1452656-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1452656-2_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

German

Application Specification

English

Application Specification

English