



**FAG****694-2Z-HLC**

Deep groove ball bearing

Deep groove ball bearing 69...-2Z, single row, shields, steel sheet metal cage

Schaeffler ID:
0554724190000

Technical information



Your current product variant

Logistical code	HLC	-
Sealing	2Z	Non-contact shield on both sides
Cage	J	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Lubricating grease	
Radial internal clearance	CN (Group N)	Normal internal clearance
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	4 mm	Bore diameter
D	11 mm	Outside diameter
B	4 mm	Width
C _r	959 N	Basic dynamic load rating, radial
C _{0r}	347 N	Basic static load rating, radial
C _{ur}	9,3 N	Fatigue load limit, radial
n _G	69.000 1/min	Limiting speed
≈m	1,8 g	Weight



Mounting dimensions

$d_{a\ min}$	4,8 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	10,2 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	0,15 mm	Maximum fillet radius

Dimensions

$r_{\min}$	0,15 mm	Minimum chamfer dimension
D_2	9,85 mm	Caliber diameter outer ring
d_2	5,6 mm	Caliber diameter inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Calculation factors

f_0	6,4	Calculation factor
-------	-----	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides