

# Poseidon GTX

GORE-TEX Fire & Rescue Boots



## Technology

DDR



RUBBER / RUBBER ABRASION  
RESISTANT OUTSOLE



## Features

<b>Standard</b>	EN ISO 15090:2012 EN ISO 20345:2011
<b>Category</b>	F2A HI3 CI AN SRC. S3 CR WR HI CI HRO SRC.
<b>Code</b>	FB300GTX
<b>Product type</b>	Fire boot
<b>Colour</b>	Black
<b>Size range</b>	UK sizes 2 - 15 continental 35 - 50
<b>Weight</b>	1.36kg
<b>Upper</b>	Full grain cow hide (2.5 - 2.7mm)
<b>Inner lining</b>	GORE-TEX® performance comfort waterproof and breathable membrane.
<b>Safety features</b>	Steel toe cap resistant up to 200 joules. Stainless steel midsole

### Additional features

Side loops for easy donning. Flex areas at rear for ease of bending and kneeling. Reflective panels. Cut resistance strip around the top of the sole unit. Ridged bump cap.

### Soling technology

Injected Dual Density Rubber soling system featuring a high compact nitrile rubber outsole and a less dense air injected midlayer for comfort and shock absorption. It is heat resistant throughout to 300°C with a high grip (SRC) outsole. This sole construction has a high bond strength between the upper and sole unit, and high abrasion resistance properties.

### Insole technology

Open Cell PU dual density PU insole. Removeable and washable.

