

ZB 5 CUS - Zack marker strip



0824962

<https://www.phoenixcontact.com/in/products/0824962>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 5.2 mm, Number of individual labels: 10, text field height: 10.5 mm, text field width: 5.15 mm

Your advantages

- Other pitches available on request
- The multi-section marking strips are easy to fit and can be easily separated if required
- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves
- Unlabeled marking strips can be custom-labeled with a plotter or by hand

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 0824962 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BG8 |
| Product key | BG8112 |
| Catalog page | Page 69 (C-5-2013) |
| GTIN | 4046356357265 |
| Weight per piece (including packing) | 1.33 g |
| Weight per piece (excluding packing) | 1.33 g |
| Customs tariff number | 49119900 |
| Country of origin | PL |

ZB 5 CUS - Zack marker strip



0824962

<https://www.phoenixcontact.com/in/products/0824962>

Technical data

Product properties

| | |
|--------------|-------------------------|
| Product type | Labeled terminal marker |
| Pitch | 5.2 mm |
| Type | high |

Marking

| | |
|-------------------------------------|----|
| Number of individual labels | 10 |
| Number of individual labels per row | 10 |
| Number of marker strips | 10 |

Mounting

| | |
|---------------|------------------------------|
| Mounting type | snap into tall marker groove |
|---------------|------------------------------|

Material specifications

| | |
|--|--------------------------------|
| Color | white (RAL 9010) |
| Material | PA |
| Flammability rating according to UL 94 | V2 |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
|---------------------------------|-------------------|

Dimensions

| | |
|-------|--------|
| Width | 5 mm |
| Pitch | 5.2 mm |

Text field


| | |
|-------------------|---------|
| Text field width | 5.15 mm |
| Text field height | 10.5 mm |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| | DIN VDE 0611 |

Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

ZB 5 CUS - Zack marker strip



0824962

<https://www.phoenixcontact.com/in/products/0824962>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
|-------------|----------|

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000761 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

ZB 5 CUS - Zack marker strip



0824962

<https://www.phoenixcontact.com/in/products/0824962>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in