

Professional Extension Cable VN 2100 IP 44, 25 m black H07RN-F 3G1,5

For use on construction sites in accordance with DGUV 203-006 (formerly BGI 608) and permanent outdoor use.



**MADE IN
GERMANY**

5 YEARS
MANUFACTURER
GUARANTEE



Product number
EAN

9161250110
4007123687787

DESCRIPTION

- With extra robust earthing contact plug and coupling with sealing cap.
- UV-resistant plug and coupling with kink protection and cable seal.
- The RN cable is very robust, oil-resistant and particularly suitable for professional use.
- Category 2 equipment (K2 DGUV 203-005): Used for harsh operating conditions with high mechanical, physical and chemical impacts.

TECHNICAL DATA

Cable quality	Rubber-Neoprene	Connection	Earthed plug/Earthed coupling
Cable length	25 m	Plug system plug	Type E and F (Protective contact with earth hole)
Cable designation	H07RN-F 3G1,5	Plug system socket/ coupling	Type F (Protective contact)
Cable colour	black	Degree of protection (IP)	IP44

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	4.02 kg
Weight of product (without packaging)	4.01 kg	Dimension LxWxH (incl. packing)	27 cm x 27 cm x 10 cm
Dimension LxWxH (without packing)	27 cm x 27 cm x 10 cm		

SCOPE OF DELIVERY

Professional Extension Cable VN 2100 IP44