



NITRILE, POWDER-FREE, SINGLE USE EXAMINATION GLOVE

High performance, powder-free, nitrile single use examination glove. Significantly stronger alternative to latex and food safe.

FEATURES

- > Comfortable with a 'second skin' feel
- High resistance to penetration and projections of many chemicals
- Textured finish on fingertips for improved grip and touch
- > Powder-free, non-sterile
- **>** AQL 1.5
- Approved for food handling
- > Latex free ideal for people with a type I latex sensitivity
- Conforms to EN455 (all parts), ASTM D6319-10 and D6124-06
- Medical device compliant (MDD 93/42/EEC)
- > Thickness: 0.10mm (5g)





For further information please visit www.globus.co.uk/icon





SUITABLE FOR

Typical Industries

- Aerospace
- Chemical
- Electronics
- Food
- Pharmaceutical
- Manufacturing
- Oil and Gas

Suitable Applications

- Chemical Handling
- Food Handling
- Handling Oily Components
- Laboratory Analysis
- Light Assembly
- Paint Spraying

CERTIFICATION












See overleaf for explanation







PRODUCT INFORMATION MATERIALS LINER: Nitrile COATING: COLOUR Blue LENGTH (mm) 240 CUFF STYLE Beaded

ORDERING DETAILS

SIZE	CODE	PACKAGING
6½-7/S 7½-8/M 8½-9/L 9½-10/XL 10½ - 11/XXL	SKYUTAH1 SKYUTAH2 SKYUTAH3 SKYUTAH4 SKYUTAH5	100 singles per box 10 boxes per case

RECOMMENDATIONS FOR USE

- USE: Single use glove. Not suitable for thermal, electrical, heavy chemical protection. Do not use near moving machines if there is a risk of entanglement
- STORAGE: Store in dry conditions in the original packaging and away from direct sunlight
- CLEANING: To clean, wipe with a damp cloth. Note: The performance characteristics of worn and laundered gloves may differ from the results shown. Inspect the gloves to ensure no damage is present.
- LIFETIME: Service life depends on the glove application and therefore cannot be specified. It is the responsibility of user to ensure the glove is suitable for its intended use

CERTIFICATION LEGENDS



RESISTANCE TO CHEMICAL PERMEATION - EN ISO 374:2016

CODE	CHEMICAL	CODE	CHEMICAL	TY
A	Methanol	J	n-Heptane	GL
В	Acetone	K	Sodium hydroxide 40%	
C	Acetonitrile	L	Sulphuric acid 96%	
D	Dichloromethane	M	65% Nitric acid	
E	Carbon Disulfide	N	99% Acetic acid	
F	Toluene	0	25% Ammonium hydroxide	
G	Diethylamine	P	30% Hydrogen peroxide	
Н	Tetrahydrofurane	S	40% Hydrofluoric acid	
1	Ethyl acetate	T	37% Formaldehyde	

TYPE OF GLOVES	BREAKTHROUGH TIME
Α	≥30 min for at least 6 chemicals
В	≥30 min for at least 3 chemicals
С	≥10 min for at least 1 chemical

Freedom from holes
Physical properties
Biological evaluation
Shelf Life



PROTECTION AGAINST MICRO-ORGANISMS EN 374-5

VIRUS = Glove has passed ISO 16604: 2004 (method B)



FOOD CONTACT DIRECTIVE EC 10/2011

EUROPE

www.globusgroup.com

E: sales@globus.co.uk T: +44 (0)161 877 4747 F: +44 (0)161 877 4746

MIDDLE EAST AND AFRICA

www.globusgroup.com/gcc

E: gcc@globusgroup.com T: +971 4 882 9962 F: +971 4 882 9963



Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES

©2021 Globus (Shetland) Ltd | SKY-DATA-UTAH-0621_3