

DELTA pushbutton device insert UP can be screwed, 1 NO 10 A 250 V



Model	
product brand name	DELTA
product designation	Pushbutton insert
design of the product	single pushbutton
design of the switching function	1 NO contact
type of composition	basic element
design of the operating mechanism	pushbutton/momentary pushbutton
General technical data	
printed marking	Without
mounting type	fixing with claw and screw
surface processing	others
material	others
Supply voltage	
operating voltage / rated value	250 V
Protection class	
protection class IP	IP20
Switching capacity	

switching capacity current	10 A
----------------------------	------

Main circuit

operating current / rated value	10 A
---------------------------------	------

Appearance

appearance	not applicable
color	miscellaneous

Product details

product component	
<ul style="list-style-type: none"> • labeling field • integrated / light source • signaling contact 	No
product feature	
<ul style="list-style-type: none"> • halogen-free • transparent 	Yes No




Number

number of actuating rockers	1
-----------------------------	---

Mechanical Design

height	70 mm
width	70 mm
depth	32 mm
mounting type	flush mounted
material / of the enclosure	metal

Certificates

General Product Approval	Declaration of Conformity	Test Certificates
 ÖVE	 VDE	 EG-Konf.
		Miscellaneous
		Type Test Certificates/Test Report

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TD2125>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TD2125>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TD2125

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

