



Positive Lock | Positive Lock 250


TE Internal #: 160759-3

Positive Lock 250, Quick Disconnects, Receptacle, 20 – 15 AWG

Wire Size, .51 – 1.65 mm² Wire Size, Mating Tab Width .25 in [6.35 mm], Straight, Brass

[View on TE.com >](#)

Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.51 – 1.65 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Terminates To	Wire & Cable
Wire/Cable Type	Regular Wire
Wire Stop	No
Insertion Force	Low
Sealable	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp



Barrel Type	Open
-------------	------

Mechanical Attachment

Mating Retention Type	Dimple
Extraction Force	7 – 100 Newton
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	2.3 – 3.3 mm[.09 – .13 in]
Receptacle Terminal Stock Thickness	.41 mm[.016 in]
Overall Length	22.3 mm[.88 in]
Wire Size	.51 – 1.65 mm²

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

UL Rating	Recognized
-----------	------------

Packaging Features

Packaging Quantity	5100
Packaging Method	Strip/Reel

Other

Comment	FLK-Wire: Normal Wire
---------	-----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free




Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2305570-1 TERMINAL CUTTER, SIDE FEED	 TE Part # 654174-1 POS.LOCK HANDTOOL	 TE Part # 626581-1 PL 250 REC 0.5-1.5 MM2 0.35X 26.54 BR	 TE Part # 2-2151182-2 OCEAN_2.0_APPLICATOR-S-090F130F
 TE Part # 2-2836571-2 OCEAN_2.0_APPLICATOR-S-090F130OV	 TE Part # 2-953615-2 MODULAR RELAY HLDR 50-60A	 TE Part # 2151182-2 OCEAN_2.0_APPLICATOR-S-090F130F	 TE Part # 282435-2 MODULAR RELAY HOUSING
 TE Part # 2836571-2 OCEAN_2.0_APPLICATOR-S-090F130OV	 TE Part # 5-2151182-2 OCEAN_2.0_APPLICATOR-S-090F130F	 TE Part # 626581-2 POSITIVE LOCK REC. MKII 250 S.	 TE Part # 7-2151182-2 OCEAN_2.0_APPLICATOR-S-090F130F



KIT

REPRESENTATION ONLY

TE Part # 7-2151182-7
OCEAN_2.0_SPARE_PART_KIT-090F130F

TE Part # 7-2836571-2
OCEAN_2.0_Applicator-S-090F130OV

KIT

REPRESENTATION ONLY

TE Part # 7-2836571-7
OCEAN_2.0_SPARE_PART_KIT-090F130OV

TE Part # 281988-3
5POS MODULAR CONN FOR MICRO RE

TE Part # 1-953615-1
MODULAR RELAY HLDR 50-60A

TE Part # 1-953615-2
MODULAR RELAY HLDR 50-60A

TE Part # 2-953615-1
MODULAR RELAY HLDR 50-60A

TE Part # 953615-1
MODULAR RELAY HLDR 50-60A

Also in the Series | Positive Lock 250

Automotive Terminals(1)

Crimp Terminal Housings(203)

Insertion & Extraction Tools(3)

Insulation Boots & Sleeves(4)

Quick Disconnects(189)

Customers Also Bought

TE Part #1-480349-0
01P CMNL PLUG HSG F/H NATL

TE Part #163301-6
MATENLOK PIN

TE Part #174777-1
PL 110 REC 20-16 AWG 0.25 X 10.4 PTBR

TE Part #964280-2
JPT A REC 2.8 Contact SRC Sn



TE Part #62895-1
[MAG-MATE POKE-IN TAB 018 TPBR](#)



TE Part #7-2151163-7
[OCEAN_2.0_SPARE_PART_KIT-055F080F](#)



TE Part #ZPF000000000120061
[CONTACT MALE 1,6 - 0,35 TO 1,82 MM2 S/A](#)



TE Part #1-1102103-7
[HA.3.STW.1.11.Z](#)

Documents

Product Drawings

[250 PL MKI REC. 20-15AWG TPBR](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_160759-3_AM.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_160759-3_AM.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_160759-3_AM.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_160759-3_06052018836_dmtec](#)

English

[MD_160759-3_06052018836_dmtec](#)

English