



WINDOW-TYPE CURRENT TRANSFORMER,
CLASS 1 250A/5A,
5VA PRIMARY CURRENT 250A, 5VA

Similar to image

General technical details:

product designation		window-type current transformers
Accuracy class / of the current transformer		class 1
Ratio input current/output current		250/5 A
Current		
• at the input / rated value	A	250
• secondary side / rated value	A	5
Operating apparent output / rated value	V·A	5
ambient temperature		
• during the operating phase	°C	-10 ... 55
Item designation		
• according to DIN 40719 extendable after IEC 204-2 / according to IEC 750		T
• according to DIN EN 61346-2		T

Mechanical design:

Width / of the push-through bus bar		
• in case of 1 bus bar / maximum	mm	30
• in case of 2 bus bars / maximum	mm	25
Outer diameter / of the push-through conductor / maximum	mm	28

Protection class IP		IP20
Depth	mm	80
Height	mm	85.5
Width	mm	64
Type of mounting		screw fixing
Design of the electrical connection / secondary side		screw-type terminals
Product equipment / touch-protection		Yes

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Global Industry Mall (Online ordering system)

<http://www.siemens.com/lowvoltage/mall>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/4NC5223-2CE20/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=4NC5223-2CE20

Tender specifications

[Datanorm](#) [GAEB81](#) [GAEB83](#) [RTF](#) [TXT](#)

last change:

May 16, 2011