



2 YEARS
MANUFACTURER
GUARANTEE



Product number
EAN

1173090100
4007123668397

TECHNICAL DATA

Luminous flux	1000 lm	Number of batteries	1
Power consumption	8.5 W	Battery type	Built-in battery pack
Colour temperature	6500 K	Battery technology	Lithium-ion
Colour rendering index	80-89 (class 1B)	Impact strength	IK08
Battery capacity	2.5 Ah	Protection class	III
Battery voltage	3.7 V	Degree of protection (IP)	IP65
Light duration max.	13 h	Colour	black/yellow
Battery charging time approx.	3 h		

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	0.38 kg
Weight of product (without packaging)	0.28 kg	Dimension LxWxH (incl. packing)	15 cm x 4.5 cm x 12.5 cm
Dimension LxWxH (without packing)	3.3 cm x 13.9 cm x 9.4 cm		