



**Part Number :** [1300130541](#)

**Product Description :** Mini-Change A-Size Bulkhead Feed-Through, 4 Poles, 7/8-16UN, Nickel Plated Brass, 0.049m (1.94") Length, 600V

**Series Number :** 130013

**Status :** Active

**Product Category :** Circular Industrial Connectors

**Engineering Number :** 1R5030



---

## Documents & Resources

### Drawings

[1300130541\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Triphenyl-phosphate per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

## Part Details

### General

Status	Active
Category	Circular Industrial Connectors
Series	130013
Description	Mini-Change A-Size Bulkhead Feed-Through, 4 Poles, 7/8-16UN, Nickel Plated Brass, 0.049m (1.94") Length, 600V
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	Mini-Change
Type	Bulkhead Feed-Through
UPC	78678845498

### Agency

CSA	LR6837
-----	--------

### Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V

### Physical

Coupling Type	Internal Thread
Gender	Male-Female
Keyway	Single
Length	0.049m

Material - Component	Nickel-plated Brass
Mounting Thread Size	7/8" - 16 UN-2A
Net Weight	32.250/g
Orientation	Straight
Panel Mount	Front
Poles	5
Temperature Range - Operating	-20° to +60°C
Wire/Cable Type	N/A
Wire Size (AWG)	N/A

---

This document was generated on Nov 05, 2025