

starmix 497

Order No.: 103686

(old Order.No. 101019 & 100289)

Equipment & Application

- **Turbo sweeping system = Sweeping twice in on step:** The disc brush system is extended with a fine-dirt brush behind it. This allows these machines to effectively sweep twice in one step. Even the most fine debris is collected.
 - **iSweep:** Thanks to the new form-fitting construction and the use of new self-lubricating sliding materials the reliability and durability of the clutch will be increased significantly → dirt resistant, maintenance-free, robust and durable.
 - The **lateral guide rollers** makes sweeping close to the edge possible and allows sweeping along kerbstones or walls and protect this areas and the machine
 - The protruding plate brushes and the **adjustable brush downholder** makes sweeping in every corner possible.
 - **Brush height adjustment:** infinitely variable for optimal sweeping on various grounds such as asphalt, concrete, slaps or for damp leaves, sand, uneven surfaces.
 - The ergonomic push handle can be adjusted up or down without the use of tools
 - **Dust reduced sweeping due to two special filters:** 2 special filters and flexible sealing lips reduce dust emission
 - Space-saving storage in upright position
 - High-quality and long-lasting disc brushes:
- 4 years warranty on brush wear**

Technical data

Working principle	Turbo sweeping system 2 disc brushes & 1 fine dirt roller brush
Brush drive	Manual
Sweeping width	97 cm
Dirt container capacity (max.)	40 liters
Sweeping performance	3.500 m²/h
Weight	15,7 kg

Application areas

For frequent professional sweeping operations for large areas up to 3.500 m².

Property Management, cleaning companies, petrol stations, workshops, car parks, courtyards, warehouses and production halls.

