# 4-1571999-4 ACTIVE

#### Alcoswitch | Alcoswitch ADP


TE Internal #: 4-1571999-4

Alcoswitch ADP, DIP & SIP Switches, Switch, Gold, Black Housing, Polyphenylene Sulfide (PPS), Auto-Insertable, 4 Switch, -30 – 85 °C, DIP

View on TE.com >



Relays, Contactors & Switches > Switches > DIP & SIP Switches



DIP & SIP Switch Product Type: Switch

DIP & SIP Switch Contact Mating Area Plating Material: Gold

DIP & SIP Switch Housing Color: Black

DIP & SIP Switch Housing Material: Polyphenylene Sulfide (PPS)

Auto-Insertable: Yes

## **Features**

## **Product Type Features**

7 P - 1 - 2 - 2 - 2 - 2 - 2 - 2 - 2 - 2 - 2	
DIP & SIP Switch Product Type	Switch
Sealed DIP & SIP Switch	No
DIP & SIP Switch Type	DIP
Actuator Style	Piano (Side Actuated)
Configuration Features	
Number of Positions	4
Number of Switches	4
Configuration (Pole-Throw)	Single Pole - Single Throw
Electrical Characteristics	
DIP & SIP Switch Voltage Rating	5 VDC
Body Features	
Actuator Color	White
Contact Features	

Solder Tail Contact Plating	Gold over Nickel
	1.2 µin
DIP & SIP Switch Contact Mating Area Plating Material	Gold
Auto-Insertable	Yes
DIP & SIP Switch Contact Current Rating	1 A



Contact Base Material	Copper Alloy
Termination Features	
Termination Post Length	4 mm[.157 in]
Mechanical Attachment	
Mounting Angle	Vertical
DIP & SIP Switch Mounting Type	Through Hole
Housing Features	
On Position	Lever Up
DIP & SIP Switch Housing Color	Black
DIP & SIP Switch Housing Material	Polyphenylene Sulfide (PPS)
DIP & SIP Switch Centerline	2.54 mm[.1 in]
Dimensions	
Height	6 mm[.236 in]
Length	12.14 mm[.478 in]
Usage Conditions	
Operating Temperature Range	-30 – 85 °C
Industry Standards	
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Method	Box & Tube, Tube
Packaging Quantity	35

## **Product Compliance**

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900



ppm.

#### Solder Process Capability

Wave solder capable to 265°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

## **Compatible Parts**









## Also in the Series | Alcoswitch ADP







DIP & SIP Switches(8)



RJ45 Connectors(1)

## Customers Also Bought



















## **Documents**

## **Product Drawings**

ADPA0404=PIANO DIP SWITCH

English

#### **CAD Files**

3D PDF

3D

**Customer View Model** 

ENG\_CVM\_CVM\_4-1571999-4\_D.2d\_dxf.zip

English

**Customer View Model** 

ENG\_CVM\_CVM\_4-1571999-4\_D.3d\_igs.zip

English

**Customer View Model** 

ENG\_CVM\_CVM\_4-1571999-4\_D.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

SWITCHES\_CORE\_PROGRAM\_CATALOG

English