



EMI & EMC Solutions > EMI Filters > Power Entry Modules > IEC Filtered Inlets, Corcom EEA Series



Filter Type: **Power Line**

Product Orientation: **Right Angle**

Leakage Current (Max) (120VAC, 60Hz): **220  $\mu$ A**

Leakage Current (Max) (250VAC, 50Hz): **380  $\mu$ A**

Current Rating: **15 A**

[All IEC Filtered Inlets, Corcom EEA Series \(0\)](#)

Features

Product Type Features

Ground Choke Option	No
Filter Type	Power Line
Output Termination Type	.250" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 320/C-14

Electrical Characteristics

Leakage Current (Max) (120VAC, 60Hz)	220 $\mu$ A
Leakage Current (Max) (250VAC, 50Hz)	380 $\mu$ A
Current Rating	15 A
Operating Voltage	250 VAC

Body Features

Product Orientation	Right Angle
---------------------	-------------

Mechanical Attachment



Panel Mount Feature Type	Snap-In
--------------------------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series |

Customers Also Bought



TE Part #2-1393640-5  
V42254B2102C963=PC612 FEDERLEI



TE Part #9-2176412-6  
5W XSM M/OX 5% 47K



TE Part #1-1622825-6  
RL73K 3A R22 5% 1K RL



TE Part #2176413-1  
5W XSM M/OX 5% 68K



TE Part #1622277-1  
LR0204 1% 75K

TE Part #1625890-7  
2W SM M/OX 5% 120K

TE Part #2-1879663-7  
H8 200R 0.1% 15PPM

TE Part #2081890-1  
EP-SMA,ADAPTER,STRAIGHT,27GHZ,  
M TO M

TE Part #6609070-1  
6FCD10 J0=F7737

TE Part #1625879-3  
FRN50 5% 1K0 (S)

Documents

Product Drawings

15EAS1=F7901N S0

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_1-6609005-0\_A1.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-6609005-0\_A1.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-6609005-0\_A1.2d\_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Corcom Combined Selector Charts

English