




Figure similar

transformer SITAS; phases: 1; Pn/Pn(S6)(kVA): 0.2 /0.85; Upri(V): 400+/-5%; Usec(V): 230; Isec(A): 0.87; F(Hz): 50...60; vector group/shielding winding: II0 /0; temperature rise/insulation class: 40 /B; IP54; connection: screw/flat-type connection; mounting: screws; EN 61558-2-1, -2-2, -2-4 >UL/CSA-recognized< >control transformer< >isolation transformer<

| General technical data               |    |                                      |
|--------------------------------------|----|--------------------------------------|
| product designation                  |    | transformer SITAS                    |
| product brand name                   |    | SIDAC                                |
| operating apparent power rated value | VA | 200                                  |
| efficiency                           |    | 0.89                                 |
| connection method for transformers   |    | II0                                  |
| certificate of suitability           |    | CE / cRUus                           |
| product function                     |    |                                      |
| • temperature monitoring             |    | No                                   |
| • insulation monitoring              |    | No                                   |
| • short-circuit and overload proof   |    | No                                   |
| number of shielding windings         |    | 0                                    |
| short-term vector power              | VA | 850                                  |
| relative short-circuit voltage       | %  | 4.93                                 |
| Inputs                               |    |                                      |
| phase number of the inputs           |    | 1                                    |
| input voltage                        |    |                                      |
| • _1 rated value                     | V  | 420                                  |
| • _2 rated value                     | V  | 400                                  |
| • _3 rated value                     | V  | 380                                  |
| electrical input frequency           |    |                                      |
| • minimum                            | Hz | 50                                   |
| • maximum                            | Hz | 60                                   |
| Outputs                              |    |                                      |
| phase number of the outputs          |    | 1                                    |
| output voltage                       |    |                                      |
| • _1 rated value                     | V  | 230                                  |
| electrical output frequency          |    |                                      |
| • maximum                            | Hz | 60                                   |
| • minimum                            | Hz | 50                                   |
| Ambient conditions                   |    |                                      |
| thermal class according to IEC 60085 |    | B                                    |
| ambient temperature rated value      | °C | 40                                   |
| protection class IP                  |    | IP54                                 |
| Mechanical data                      |    |                                      |
| type of electrical connection        |    |                                      |
| • at output for main current circuit |    | screw-type terminals / tab terminals |
| • at input for main current circuit  |    | screw-type terminals / tab terminals |

|                                    |   |          |
|------------------------------------|---|----------|
| fastening method                   |   | screws   |
| construction form of the iron core |   | EI 96/58 |
| width                              | m | 0.244    |
| height                             | m | 0.245    |
| depth                              | m | 0.23     |

Certificates/ approvals

|                          |       |             |
|--------------------------|-------|-------------|
| General Product Approval | other | Environment |
|--------------------------|-------|-------------|



[Confirmation](#)

[Environmental Confirmations](#)

Further information

Information on the packaging  
<https://support.industry.siemens.com/cs/ww/en/view/109813875>  
Information for data generation and storage  
<https://support.industry.siemens.com/cs/ww/en/view/109995012>  
Information- and Downloadcenter (Catalogs, Brochures,...)  
<https://www.siemens.com/ic10>  
Industry Mall (Online ordering system)  
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4AM4042-5AT10-0FD0>  
Cax online generator  
<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AM4042-5AT10-0FD0>  
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)  
<https://support.industry.siemens.com/cs/ww/en/ps/4AM4042-5AT10-0FD0>  
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)  
[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=4AM4042-5AT10-0FD0&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AM4042-5AT10-0FD0&lang=en)

last modified: 4/2/2025