

Dust Extractor XGT®

VC002GL

40Vmax • 230 mbar • 8 L • L

XGT® Battery powered dust extractor for cleaning.

A versatile dust extractor that runs on with XGT® battery. The batteries can be connected in parallel. It Matches filter class: 8L HEPA GYUPPA. Tank capacity is 8 L which enables continuous cleaning work.



Technical specifications

Vacuum hose length	2,5 / 3,5 m
Vacuum hose diameter	28 / 38 mm
Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Air volume	2,9 m³/min
Max. sealed suction	230 mbar
Suction power	205 W
AWS ready	✓
Continuous Use XGT® 40V Max / 5.0 Ah X2	28 - 220 min
Tank Capacity for Dust	8 L
Sound Pressure Level (L _{pA})	≤ 70 dB(A)
Product net weight	7,9 kg
Noise Uncertainty (K Factor)	2,5 dB(A)
Tool weight with battery	8,3 - 11,4 kg
Product Dimensions (L x W x H):	366 x 334 x 425

User benefits

- Auto-start Wireless System (AWS) connects to power tool with Bluetooth
- HEPA Filter is used to capture very fine particles effectively
- Quiet operation for operator comfort
- Flat top design for space saving in storage
- Carry handle for easy transportation
- Approved for Dust Class L in accordance with the EU standard
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.uk.com



Related products

Optional AC

191V68-0
Damper Set



191V69-8
Pre Filter Set



191V70-3
Powder Filter H(HEPA) set



192562-3
Curved hand tube 38 mm



192563-1
Straight Pipe Ø 38 mm



Other

User manual

Parts drawing