

Stockinette Specifications

	<u>1/7</u>	<u>1/8</u>	<u>1/10</u>	<u>1/12</u>	<u>1/14</u>	<u>1/16</u>	<u>1/18</u>	<u>1/20</u>	<u>1/24</u>	<u>1/30</u>	<u>1/40</u>	<u>1/50</u>	<u>1/60</u>
<u>1/7</u>	3.5	3.7	4.1	4.4	4.7	4.9	5.0	5.2	5.4	5.7	6.0	6.1	6.3
<u>1/8</u>	3.7	4.0	4.4	4.8	5.1	5.3	5.5	5.7	6.0	6.3	6.7	6.9	7.1
<u>1/10</u>	4.1	4.4	5.0	5.5	5.8	6.2	6.4	6.7	7.1	7.5	8.0	8.3	8.6
<u>1/12</u>	4.4	4.8	5.5	6.0	6.5	6.9	7.2	7.5	8.0	8.6	9.2	9.7	10.0
<u>1/14</u>	4.7	5.1	5.8	6.5	7.0	7.5	7.9	8.2	8.8	9.5	10.4	10.9	11.4
<u>1/16</u>	4.9	5.3	6.2	6.9	7.5	8.0	8.5	8.9	9.6	10.4	11.4	12.1	12.6
<u>1/18</u>	5.0	5.5	6.4	7.2	7.9	8.5	9.0	9.5	10.3	11.3	12.4	13.2	13.8
<u>1/20</u>	5.2	5.7	6.7	7.5	8.2	8.9	9.5	10.0	10.9	12.0	13.3	14.3	15.0
<u>1/24</u>	5.4	6.0	7.1	8.0	8.8	9.6	10.3	10.9	12.0	13.3	15.0	16.2	17.1
<u>1/30</u>	5.7	6.3	7.5	8.6	9.5	10.4	11.3	12.0	13.3	15.0	17.1	18.8	20.0
<u>1/40</u>	6.0	6.7	8.0	9.2	10.4	11.4	12.4	13.3	15.0	17.1	20.0	22.2	24.0
<u>1/50</u>	6.1	6.9	8.3	9.7	10.9	12.1	13.2	14.3	16.2	18.8	22.2	25.0	27.3
<u>1/60</u>	6.3	7.1	8.6	10.0	11.4	12.6	13.8	15.0	17.1	20.0	24.0	27.3	30.0

Grade.....Medium.....Part No.....M.....

Yarn type	Cotton
Min yarn count	6's cotton count
Max yarn count	8's cotton count
Machine Nos.	
Min. No. Needles	264
Max. No. Needles	264
Gear Wheels	
Courses per inch	10
Stretch Width	

Comments ___ Usually 7's resultant

PMR 800 is an 800 gram roll subject to mill condition.