

Linetrimmer LXT®

DUR192L

18V • 4 500 – 6 000 min⁻¹ • 300 mm

Brushless 2-speed trimmer for trimming green spaces

An efficient brushless 2-speed line trimmer with a loop handle. Cutting width is 300 mm. Low vibration and good ergonomics ensure a good user experience.



Technical specifications

Nominal Battery Voltage	18 V
No load speed	0 - 4500 / 6000 min ⁻¹
Cutting width	300 mm
Tool weight with battery	2,7 - 3,0 kg
Nylon line- Diameter	2,0 mm
Sound Power Level (L _{WA})	86,3 dB(A)
Sound Pressure Level (L _{pA})	74,8 dB(A)
Noise Uncertainty (K Factor)	3,7 dB(A)
Product Dimensions (L x W x H):	1623 x 186 x 246 mm
Brushless Motor	✓
Voltage LXT	✓
Spindle Thread	M10 x 1,25 LH
Handle Type	L
Vibration Level, Nyloncord	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor),	1,5 m/s ²

User benefits

- Brushless maintenance-free and long-life motor
- Constant speed control maintains constant speed under load
- Variable 2-speed options allows the user to match speed to application
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Electric brake for maximum productivity and increased operator safety
- Soft start feature for added motor protection
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

Optional AC

127508-0

Band Assembly



191D89-4

Trimmer head Tap & Go 2,0 mm, M10



198893-8

Trimmer Head 2,0 mm, M10 x 1.25



783202-0

Hex Wrench 4Mm



Other

User manual

Parts drawing