

Parker Product Datasheet



Direct operated DFplus control valves D1FP in NG06 (CETOP 03) and D3FP in NG10 (CETOP 05) meet highest requirements in terms of dynamics combined with high flow. Optionally with IO-Link Class B or EtherCAT interface.

PART NUMBER: D1FPE50MA9NB00
SEAL MATERIAL: NBR
SIGNAL OUTPUT: ± 10 V
FLOW RATE: 40 L/Min
MARKING: Standard
PORT CONNECTION: NG06 / CETOP 03
SIGNAL INPUT: ± 10 V
SENSOR TYPE: omit
CONNECTION TYPE: 6 + PE
SPOOL POSITION: P to A
SPOOL CODE: E50M

PRODUCT OVERVIEW

The direct operated control valves D1FP and D3FP show extremely high dynamics combined with maximum flow. It is the preferred choice for highest accuracy in positioning of hydraulic axis and controlling of pressure and velocity.

Driven by the patented VCD actuator, the D1FP / D3FP reach the frequency response of real servo valves. At power-down the spool moves in a defined position. All common input signals are available. All valves have an IO-Link Class A interface as standard.

Version with IO-Link Class B interface

D1FP and F3FP with IO-Link class B interface meets the requirements for a modern and cost-effective interface that enables power supply and digital actuation and/or communications via an M12 interface.

Version with EtherCAT interface

The D1FP / D3FP with EtherCAT interface fulfills the requirements of modern communication between valve and main control. Due to high data transmission speed and short cycle times, the high dynamics of the DFplus valves can be also utilized within the fieldbus system.

Version with freely configurable secondary control loop

DFplus valves D1FP*D and D3FP*D with a freely configurable secondary control loop provide highly dynamic control without the need for an additional external controller. Using integrated electronics in combination with an analog sensor, the valves ensure precise pressure or position control. Actuation and communication can be performed either via analog signals or digitally through an IO-Link Class A or Class B interface.

Markets:

- Industrial
- Machine tools
- Molding
- Marine (non-military)

Features/benefits:

- Real servovalve dynamics (-3 dB / 350 Hz at ± 5 % input signal) - ideal for demanding applications, ensures optimized cycle times
- Very good repeatability - improved process and product accuracy
- Robust valve design - minimized failure
- Digital electronics - can be easily adapted to the application, resulting in flexible use
- Short delivery time - no storage necessary
- Defined spool positioning at power-down - optional P-A/B-T or P-B/A-T or center position (for overlapped spools)
- IO-Link interface for parametrizing
- RGB diode for optical status check
- NFC interface
- With EtherCAT interface upon request - high data speeds, short cycle times
- Optionally with freely configurable supervising control circuit (D1FP*D, D3FP*D)

Applications:

- General presses

- Machine tool
- Blow molding
- Marine Diesel fuel injection/exhaust valve control

Additional information EtherCAT version

The valve is actuated and monitored by the EtherCAT interface. Actual value (spool position), temperature, operating hours and different error messages are available as diagnostic signals. The valve parameters are factory set and can be adapted with the Parker ProPxD software via the parametrizing interface.

In addition to the fieldbus communication, the valves provide the range of functions of the standard version including analogue command signal and diagnostic spare stroke. Thus they can be operated independent of the fieldbus control, particularly during commissioning and maintenance.

Note: The version with explosion protection is no longer available.

TECH SPECIFICATIONS

INGRESS PROTECTION RATING	IP65 in accordance with EN 60529
BODY MATERIAL	Cast Iron
MOUNTING STYLE	CETOP RP121
WEIGHT	3.6 kg
POWER SUPPLY VOLTAGE	24 V Nominal (tolerance range 22 ... 30)
SEAL MATERIAL	NBR
HYSTERESIS	< 0.05 %
MAXIMUM KINEMATIC VISCOSITY	400 cSt
VIBRATION RESISTANCE	15 Shock Acc. IEC 60068-2-27
MOUNTING STYLE	NFPA
FOR FLUID TYPE	Hydraulic Oil according to DIN 51524 ... 535
MOUNTING POSITION	Unrestricted
OPERATION TYPE	Direct

MOUNTING STYLE	ISO 4401
FLOW RATE	40 L/min
VIBRATION RESISTANCE	20 (RMS) Random Noise 20...2000 Hz Acc. IEC 60068-2-64
FILTER EFFICIENCY RATING	ISO 4406 18/16/13
VIBRATION RESISTANCE	10 Sinus 5...2000 Hz Acc. IEC 60068-2-6
MAXIMUM FLUID TEMPERATURE	60 °C
ELECTRONICS TYPE	Onboard
MINIMUM FLUID TEMPERATURE	-25 °C
MAXIMUM OPERATING PRESSURE	350 bar
PORT CONNECTION	NG06 / CETOP 03
LEAK RATE	< 400 ml/min
RESPONSE TIME	< 3.5 ms
MOUNTING STYLE	DIN 24340
FUNCTION	Proportional
MINIMUM KINEMATIC VISCOSITY	20 cSt
MEDIA	Hydraulic Oil
MAXIMUM AMBIENT TEMPERATURE	60 °C
MINIMUM AMBIENT TEMPERATURE	-20 °C
POWER SUPPLY VOLTAGE	Electric Shut-off at < 19 V Nominal (tolerance range 22 ... 30)
BRAND	Parker
ACTUATION TYPE	VCD®-actuator
APPLICATION	Industrial Hydraulic
PRODUCT SERIES	Proportional DC Valve
POWER SUPPLY VOLTAGE	Surge Free V % Eff.

PRESSURE DIFFERENTIAL	35 bar
DIVISION	Hydraulic Valve Systems Division Europe
TECHNOLOGY	Hydraulics
FUNCTION	3-Way
POWER SUPPLY VOLTAGE	Ripple < 5 V % Eff.
MOUNTING TYPE	Subplate
MAXIMUM FLOW RATE	90 L/min
DIVISION	Hydraulic Valve Systems Division Europe
VALVE TYPE	Proportional DC Valve