

# Eaton 255913

Catalog Number: 255913

Eaton Moeller® series T5B Main switch, T5B, 63 A, surface mounting, 3 contact unit(s), 3 pole + N, 1 N/O, 1 N/C, Emergency switching off function, With red rotary handle and yellow locking ring, UL/CSA



### General specifications

Product Name	Catalog Number
Eaton Moeller® series T5B Main switch	255913
EAN	Product Length/Depth
4015082559137	240 mm
Product Height	Product Width
204 mm	160 mm
Product Weight	Certifications
1.358 kg	VDE 0660
	UL
	UL File No.: E36332
	CSA-C22.2 No. 94
	CE
	CSA
	IEC/EN 60947-3
	UL Category Control No.: NLRV
	CSA Class No.: 3211-07
	UL 60947-4-1
	CSA-C22.2 No. 60947-4-1-14
	IEC/EN 60204
	IEC/EN 60947
	CSA File No.: 012528

## Product specifications

### Product Category

Main switch

### Features

Version as emergency stop installation

Version as maintenance-/service switch

Version as main switch

### Actuator color

Red

### 10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

### 10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

### 10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

### 10.2.2 Corrosion resistance

Meets the product standard's requirements.

### 10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

### 10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

### 10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

### 10.2.4 Resistance to ultra-violet (UV) radiation

UV resistance only in connection with protective shield.

### 10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

### 10.2.6 Mechanical impact

## Resources

### Brochures

Brochure - T Rotary Cam switch and P Switch-disconnector

### Catalogs

P Switch-disconnectors and T Rotary cam switches catalogue  
CA042001EN

### Declarations of conformity

DA-DC-00004925.pdf

DA-DC-00004897.pdf

### Drawings

eaton-rotary-switches-padlock-t0-main-switch-dimensions.eps

eaton-rotary-switches-p3-main-switch-dimensions-009.eps

eaton-general-switch-t0-main-switch-symbol.eps

eaton-rotary-switches-t0-main-switch-symbol.eps

eaton-general-totally-insulated-t0-main-switch-symbol.eps

### eCAD model

ETN.255913.edz

### Installation instructions

IL03801009Z

### Installation videos

Eaton's P Switch-disconnectors used in a factory

### mCAD model

DA-CD-bauform13

DA-CS-bauform13

### Product notifications

MZ008006ZU\_Orderform\_Customized\_Switch.pdf

MZ008005ZU\_Orderform\_Customized\_Switch.pdf

### Wiring diagrams

eaton-rotary-switches-switch-t0-main-switch-wiring-diagram-004.eps

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.7 Inscriptions

Meets the product standard's requirements.

#### 10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.4 Clearances and creepage distances

Meets the product standard's requirements.

#### 10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

#### 10.8 Connections for external conductors

Is the panel builder's responsibility.

#### 10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

#### 10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

#### 10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

#### Fitted with:

Red rotary handle and yellow locking ring

#### Operating frequency

1200 Operations/h

#### Pollution degree

3

#### Climatic proofing

Damp heat, constant, to IEC 60068-2-78

Damp heat, cyclic, to IEC 60068-2-30

#### Rated impulse withstand voltage (Uimp)

6000 V AC

#### Rated operational power star-delta at 500 V, 50 Hz

37 kW

Rated operational power star-delta at 690 V, 50 Hz

22 kW

Rated permanent current at AC-21, 400 V

63 A

Rated permanent current at AC-23, 400 V

63 A

Rated uninterrupted current (Iu)

63 A

Static heat dissipation, non-current-dependent Pvs

0 W

Switching angle

90 °

Switching power at 400 V

30 kW

Voltage per contact pair in series

60 V

Rated operational power at AC-3, 500 V, 50 Hz

22 kW

Device construction

Complete device in housing

Rated short-time withstand current (Icw)

1.3 kA

1,3 kA, Contacts, 1 second

Electrical connection type of main circuit

Screw connection

Design

8901

Mounting position

As required

Actuator type

Door coupling rotary drive

Ambient operating temperature - max

40 °C

Ambient operating temperature - min

-25 °C

Ambient operating temperature (enclosed) - max

40 °C

Ambient operating temperature (enclosed) - min

-25 °C

Assigned motor power at 115/120 V, 60 Hz, 1-phase

3 HP

Assigned motor power at 200/208 V, 60 Hz, 1-phase

7.5 HP

Assigned motor power at 200/208 V, 60 Hz, 3-phase

15 HP

Assigned motor power at 230/240 V, 60 Hz, 1-phase

10 HP

Assigned motor power at 230/240 V, 60 Hz, 3-phase

15 HP

Assigned motor power at 460/480 V, 60 Hz, 3-phase

40 HP

Assigned motor power at 575/600 V, 60 Hz, 3-phase

40 HP

Equipment heat dissipation, current-dependent  $P_{vid}$

4.5 W

Heat dissipation capacity  $P_{diss}$

0 W

Heat dissipation per pole, current-dependent  $P_{vid}$

4.5 W

Number of auxiliary contacts (change-over contacts)

0

Number of auxiliary contacts (normally closed contacts)

1

Rated conditional short-circuit current ( $I_q$ )

2 kA

Overvoltage category

III

Control circuit reliability

1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)

Degree of protection (front side)

IP65

Number of poles

4

#### Mounting method

Surface mounting

#### Degree of protection

NEMA 12

#### Suitable for

Branch circuits, suitable as motor disconnect, (UL/CSA)

Ground mounting

#### Functions

Interlockable

Emergency switching off function

#### Number of switches

1

#### Safe isolation

440 V AC, Between the contacts, According to EN 61140

#### Screw size

M6, Terminal screw

#### Shock resistance

15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms

#### Lifespan, mechanical

500,000 Operations

#### Load rating

$2 \times I_e$  (with intermittent operation class 12, 25 % duty factor)

$1.3 \times I_e$  (with intermittent operation class 12, 60 % duty factor)

$1.6 \times I_e$  (with intermittent operation class 12, 40 % duty factor)

#### Terminal capacity

1 x (1 - 25) mm<sup>2</sup>, flexible with ferrules to DIN 46228

2 x (1.5 - 10) mm<sup>2</sup>, flexible with ferrule to DIN 46228

2 x (2.5 - 16) mm<sup>2</sup>, solid or stranded

12 - 4 AWG, solid or flexible with ferrule

1 x (2.5 - 35) mm<sup>2</sup>, solid or stranded

#### Switching capacity (main contacts, general use)

63 A, Rated uninterrupted current max. (UL/CSA)

#### Safety parameter (EN ISO 13849-1)

B10d values as per EN ISO 13849-1, table C.1

#### Number of auxiliary contacts (normally open contacts)

1

Number of contact units

3

Number of contacts in series at DC-23A, 120 V

3

Number of contacts in series at DC-23A, 24 V

1

Number of contacts in series at DC-23A, 240 V

6

Number of contacts in series at DC-23A, 48 V

2

Number of contacts in series at DC-23A, 60 V

3

Rated breaking capacity at 220/230 V (cos phi to IEC 60947-3)

520 A

Rated breaking capacity at 400/415 V (cos phi to IEC 60947-3)

600 A

Rated breaking capacity at 500 V (cos phi to IEC 60947-3)

480 A

Rated breaking capacity at 660/690 V (cos phi to IEC 60947-3)

340 A

Rated making capacity up to 690 V (cos phi to IEC/EN 60947-3)

800 A

Rated operating voltage (Ue) - max

690 V

Rated operating voltage (Ue) - min

690 V

Rated operational voltage (Ue) at AC - max

690 V

Short-circuit current rating (high fault)

100 A, Class J, max. Fuse, SCCR (UL/CSA)

10 kA, SCCR (UL/CSA)

Short-circuit protection rating

80 A gG/gL, Fuse, Contacts

Rated operational current (Ie) at AC-21, 440 V

63 A

Rated operational current (Ie) at AC-23A, 230 V

63 A

Rated operational current (Ie) at AC-23A, 400 V, 415 V

63 A

Rated operational current (Ie) at AC-23A, 500 V

33 A

Rated operational current (Ie) at AC-23A, 690 V

23.8 A

Rated operational current (Ie) at AC-3, 220 V, 230 V, 240 V

51 A

Rated operational current (Ie) at AC-3, 380 V, 400 V, 415 V

41 A

Rated operational current (Ie) at AC-3, 500 V

33 A

Rated operational current (Ie) at AC-3, 660 V, 690 V

17 A

Rated operational current (Ie) at DC-1, load-break switches I/r = 1 ms

63 A

Rated operational current (Ie) at DC-13, control switches L/R = 50 ms

25 A

Rated operational current (Ie) at DC-23A, 120 V

25 A

Rated operational current (Ie) at DC-23A, 24 V

50 A

Rated operational current (Ie) at DC-23A, 240 V

20 A

Rated operational current (Ie) at DC-23A, 48 V

50 A

Rated operational current (Ie) at DC-23A, 60 V

50 A

Rated operational current (Ie) star-delta at AC-3, 220/230 V

63 A

Rated operational current (Ie) star-delta at AC-3, 380/400 V

63 A

Rated operational current (Ie) star-delta at AC-3, 500 V

57.2 A

Rated operational current (Ie) star-delta at AC-3, 690 V

29.4 A



Rated operational current for specified heat dissipation (In)

63 A

Rated operational power at AC-23A, 220/230 V, 50 Hz

18.5 kW

Rated operational power at AC-23A, 400 V, 50 Hz

30 kW

Rated operational power at AC-23A, 500 V, 50 Hz

22 kW

Rated operational power at AC-23A, 690 V, 50 Hz

22 kW

Rated operational power at AC-3, 380/400 V, 50 Hz

22 kW

Rated operational power at AC-3, 415 V, 50 Hz

22 kW

Rated operational power at AC-3, 690 V, 50 Hz

15 kW

Rated operational power star-delta at 220/230 V, 50 Hz

18.5 kW

Rated operational power star-delta at 380/400 V, 50 Hz

30 kW

Tightening torque

35.4 lb-in, Screw terminals

4 Nm, Screw terminals

Uninterrupted current

Rated uninterrupted current  $I_u$  is specified for max. cross-section.

Rated Switching Capacity

10 HP at 240 V AC, single-phase

15 HP at 200 V AC, three-phase

15 HP at 240 V AC, three-phase

3 HP at 120 V AC, single-phase

40 HP at 480 V AC, three-phase

40 HP at 600 V AC, three-phase

7.5 HP at 200 V AC, single-phase



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)