



Connectors > D-Shaped Connectors > D-Sub Connectors > IDC D-Sub Connectors > IDC D-Sub: Connector Kit, Plug, Wire to Wire, Signal, 2.77 mm



Connector & Housing Type: **Plug**

Solid Wire Size: **.13 – .32 mm²**

Shielded: **Yes**

Connector System: **Cable-to-Cable**

[All IDC D-Sub: Connector Kit, Plug, Wire to Wire, Signal, 2.77 mm \(17\)](#)

Features

Product Type Features

Grade	Standard
Grounding Indents	With
Shell Type	Front Metal Shell
Connector & Housing Type	Plug
Connector System	Cable-to-Cable
Connector Product Type	Connector Kit
D-Sub Shell Size	3
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Pre-Assembled	No
Number of Positions	25
Number of Rows	2
Compatible With Wire & Cable Type	Discrete Wire, Round Jacketed Cable

Body Features

Shield Material	Steel
Color	Black
Shell Material	Steel



Insert Material	Thermoplastic
Shell Plating Material	Tin
Shield Plating Material	Tin

Contact Features

Contact Type	Pin
Contact Mating Area Plating Thickness	.76 µm[30 µin]
Contact Mating Area Plating Material	Gold
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
D-Sub Contact Size	20
Contact Current Rating (Max)	5 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Mating Connector Lock	With
Mounting Angle	Straight
Mating Connector Lock Type	Mounting Holes
Wire Insulation Support	With
PCB Mount Retention Type	None
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Enclosure	With
Centerline (Pitch)	1.38 mm[.054 in]

Dimensions

Cable Outside Diameter	4.19 – 11.56 mm[.165 – .455 in]
Cable Insulation Diameter Range	4.19 – 11.56 mm[.165 – .455 in]
Accepts Cable Diameter (Max)	11.56 mm[.455 in]
Accepts Wire Insulation Diameter Range	1.52 mm[.06 in]
Solid Wire Size	.13 – .32 mm²
Wire Size	.15 – .4 mm²

Usage Conditions



Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Shielded	Yes
Circuit Application	Signal

Industry Standards

Insert Flammability Rating	UL 94V-0
----------------------------	----------

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Other

Comment	Components shipped unassembled, each part bulk-packaged., Maximum cable diameter after jacket and braid removed.
---------	--

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts

 TE Part # CAT-025-DRAVS3277 D-Sub Recpt Assy: Vert, Size 3, 2.77mm	 TE Part # CAT-AM7-248H5 IDC D-Sub: Receptacle Assembly, Wire to Wire, Signal, 2.77 mm	 TE Part # CAT-AM7-253 IDC D-Sub: Receptacle Assembly, Low Profile, Signal, 2.77 mm	 TE Part # CAT-023-DRARS3277 D-Sub Receptacle Assy: RA, Size3, 2.77 mm
 TE Part # CAT-026-RAVSAP3277 Recpt Assy Vert Size3 Action Pin, 2.77 mm	 TE Part # CAT-AM7-248H6 IDC D-Sub: Receptacle Kit, Wire to Wire, Signal, 2.74 mm	 TE Part # 58074-1 MTA 50/100/156 MANUAL TOOL FRAME	 TE Part # 747548-8 KIT,RCPT,25P,HDE,SHLD HDWRE
 TE Part # 7-1393740-2 V42254A2216B225=SUB D FEDERLEI	 TE Part # 8-1393480-3 V23529B1223B225=SUB D FEDERLEI	 TE Part # 3-1393480-0 V23529B1122B225=SUB D FEDERLEI	 TE Part # 1-1393480-9 V23529B1121B225=SUB D FEDERLEI
 TE Part # 8-1393480-4 V23529B1223B237=SUB D FEDERLEI	 TE Part # 1393481-2 V23529B1225B225=SUB D FEDERLEI	 TE Part # 5-1393480-7 V23529B1221B225=SUB D FEDERLEI	 TE Part # 9-1393480-2 V23529B1224B225=SUB D FEDERLEI
 TE Part # 608868-1 HDE HT PKG FOR SUB D	 TE Part # 7-338315-2 25POS.HD20 REC.ASSY	 TE Part # 8-338315-2 25P.HDP20 REC.ASSY	 TE Part # 9-338315-2 25POS.HD20 REC.ASSY

Also in the Series | **AMPLIMITE HDE**



Crimp D-Sub Connectors(1)



D-Sub Connector Contacts(13)



IDC D-Sub Connectors(75)



Insertion & Extraction Tools(2)

Customers Also Bought



TE Part #DT04-2P
DEUTSCH DT HOUSINGS



TE Part #W2S
DEUTSCH DT WEDGELOCKS




TE Part #282104-1
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING



TE Part #206070-8
CABLE CLAMP KIT #17



TE Part #0460-202-16141
DEUTSCH SOLID CONTACTS



TE Part #281934-2
SINGLE WIRE SEAL

Documents

Product Drawings

KIT,PLUG,25P,HDE,SHLD HDWRE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_747547-9_J.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_747547-9_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_747547-9_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

Product Specifications

Application Specification

English

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English

UL Report

English