



Product data sheet

Power tools for trade & industry

HGS 57/50 Ls

INDUSTRIAL HGS 57/50 Ls



Rod handle, central drive end spindle length up to 480 mm possible

The most important data

Permitted grinding stone diameter	50 mm
No-load speed	12,000 rpm
Rated power, output	270 W

Part Number 0 602 238 104

Technical data

Technical data

Frequency	200 Hz
Voltage	135 V
Permitted grinding stone diameter	50 mm
No-load speed	12,000 rpm
Rated power, input	400 W
Rated power, output	270 W
Rated current	3.3 A
Weight as per EPTA	2.2 kg
Toolholder, drive end	Collet 6 mm
Switch version	Safety switch

Product data sheet

Power tools for trade & industry



BOSCH
Invented for life

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

