


FEATURES

- **Annealed Copper Conductor:** Provides superior conductivity and long-lasting performance
- **Polyvinyl Chloride Jacket:** Offers protection against environmental factors and enhances durability
- **Plain Conductor Type:** Ensures ease of installation and consistent electrical performance
- **30/0.25 Core Strands:** Delivers flexibility and strength for demanding applications
- **Wide Temperature Range:** Operates efficiently between -15 °C and 70 °C
- **500 V Voltage Rating:** Suitable for a variety of electrical applications
- **10.5 mm Outside Diameter:** Facilitates easy routing and installation

RS PRO 1.5 mm² Flexible Cable, 100 m

RS Stock No: 606-069



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for reliable electrical connections in various industrial settings. With a conductor made from annealed copper, it ensures excellent conductivity and durability. The cable is suitable for installations requiring flexibility and resilience, making it ideal for complex wiring systems.

General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	Black
Product Type	Flexible Cable

Mechanical Specifications

Cable CSA	1.5 mm ²
Cable Length	100 m
Core Strands	30/0.25
Jacket Material	Polyvinyl Chloride
Number of Cores	4
Outside Diameter	10.5 mm

Operation Environment Specifications

Maximum Operating Temperature	70 °C
Minimum Operating Temperature	-15 °C

Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

Electrical Specifications

Voltage	500 V
---------	-------