

**KEMET Part Number: C0402C209C5GACTU**  
(C0402C209C5GAC7867)

Capacitor, Ceramic, SMD, MLCC, Ultra-Stable, Low Loss, Class I, 2 pF, +/-0.25pF Tol, 50 V, C0G, 0402 (1005 metric)



| General Information      |  |
|--------------------------|--|
| Supplier:                | KEMET                                      |
| Application:             | Standard Chip                              |
| Chip Size:               | 0402 (1005 metric)                         |
| Temperature Coefficient: | C0G  |
| Part Type Description:   | SMD, MLCC, Ultra-Stable, Low Loss, Class I |
| Termination Type:        | Tin (Sn)                                   |
| Marked:                  | No   |
| RoHS:                    | Yes  |

| Dimensions (mm) |           |           |
|-----------------|-----------|-----------|
| Symbol          | Dimension | Tolerance |
| L               | 1         | +/-0.05   |
| W               | 0.5       | +/-0.05   |
| T               | 0.5       | +/-0.05   |
| B               | 0.3       | +/-0.1    |
| S               | 0.3       | MIN       |

| Packaging Specifications |            |
|--------------------------|------------|
| Package Kind:            | T&R        |
| Package Size:            | 7in        |
| Package Type:            | Paper Tape |
| Package Quantity:        | 10000      |

| Specifications         |   |
|------------------------|---|
| Capacitance:           | 2 pF  |
| Voltage:               | 50 V  |
| Tolerance:             | +/-0.25pF   |
| Temperature Range:     | -55/+125C   |
| Dissipation Factor:    | 0.1%  |
| Failure Rate:          | NA  |
| Aging Rate:            | 0% loss/decade hour                                     |
| Insulation Resistance: | 100 GOhm  |
| Dielectric Strength:   | 125 V   |
| Miscellaneous:         | Note: KEMET 50V rated parts may be operated at 63 Volts |