

# KSA100EV4254

Vertical distribution length, Canalis KSA100, aluminium, 100A, fixed length 2.5m, 4 outlets, 3L+N+PE, white RAL9001



## Main

Range	Canalis
Device short name	KSA
Offer type	Rising main
Product or component type	Busbar trunking
Busbar description	Vertical distribution length
Product compatibility	Canalis KSA busbar trunking 100...250 A
Conductors material	Aluminium
Busbar trunking polarity	3L + N + PE
Number of tap-off outlets	4
[Ie] rated operational current	100 A at 35 °C
IP degree of protection	IP55 conforming to IEC 60529
Mounting mode	By screws
Dimension type	Fix
Length	2.5 m
Colour	White (RAL 9001)

## Complementary

Number of poles	4
Neutral position	Right
Mounting position	Vertical
[Ue] rated operational voltage	230...690 V
Network frequency	50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ui] rated insulation voltage	690 V
[Icw] rated short-time withstand current	2.6 kA
[Ipk] rated peak withstand current	15.7 kA
Electrical connection	Lubricated sliding contact
Width	54 mm
Height	146 mm
Net weight	8.5 kg
Tap-off unit interval	500 mm
Radiated magnetic field	0.22 µT
Thermal stress limit	6800 kA².s
THDI	0...15 % 100 A 15...33 % 80 A 33...100 % 63 A
Maximum voltage drop	<0.138 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.13 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.118 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.106 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Standards	IEC 61439-1 IEC 61439-6

## Environment

IK degree of protection	IK08 conforming to IEC 62262
Ambient air temperature for operation	35 °C (without derating) 55 °C (with derating factor)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins