

OJ-SS-109DM,000

✕ OBSOLETE

OEG | OEG Miniature PCB Relay OJ/OJE

TE Internal #: 1-1419129-5

TE Internal Description: OJ-SS-109DM,000

[View on TE.com >](#)



Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | [OEG Miniature PCB Relay OJ/OJE](#)



General Purpose Power Relays(67)



PCB Relays(67)


Customers Also Bought



TE Part #1969730-3
EP2.5 SHROUDED HDR ASSY 3P
VERTICAL



TE Part #1969730-7
EP2.5 SHROUDED HDR ASSY 7P
VERTICAL



TE Part #1-1586040-2
12P VAL-U-LOK VRT HDR W/P V0



TE Part #1969730-4
EP2.5 SHROUDED HDR ASSY 4P
VERTICAL




TE Part #1969730-5
EP2.5 SHROUDED HDR ASSY 5P
VERTICAL




TE Part #1376387-1
5mm B-T-W Conn. 6P(2row) HDR A




TE Part #1969730-6
EP2.5 SHROUDED HDR ASSY 6P
VERTICAL



TE Part #178487-1
UP 3.96 4P TAB HDR NAT TYPE 1



TE Part #1586040-4
4P VAL-U-LOK VRT HDR W/P V0



TE Part #5068234005
CGPT-25.4/12.7-4-SP

Documents

Product Drawings

OJ-SS-109DM,000

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1419129-5_E4.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-1419129-5_E4.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1419129-5_E4.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[OJ_OJE Series Relay Data Sheet English](#)

English

Product Specifications

[OJ-SS-109DM,000 Spec Sheet](#)

Japanese

[Definitions General Purpose Relays](#)

English