

## Housing - HC-B 10-SFQD-52/M2PG16 - 1771419


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Box mounting base, for double locking latch, height 52 mm, with screw connection, 2x Pg16, with protective covers



### Key commercial data

|                                      |  |
|--------------------------------------|--|
| Packing unit                         | 10 pc  |
| GTIN                                 | <br>4 017918 036140 |
| Weight per Piece (excluding packing) | 252.5 g  |
| Custom tariff number                 | 85389099   |
| Country of origin                    | Germany  |

### Technical data

#### Dimensions

|                         |                            |
|-------------------------|----------------------------|
| Height                  | 52 mm                      |
| Width                   | 52 mm                      |
| Length                  | 93 mm                      |
| Wrench size, union nut  | 22 mm                      |
| External cable diameter | 7.5 mm ... 15 mm (Cable 1) |
|                         | 7.5 mm ... 15 mm (Cable 2) |

#### Ambient conditions

|                                      |                        |
|--------------------------------------|------------------------|
| Degree of protection of housing (IP) | IP65 (When plugged in) |
| Ambient temperature (operation)      | -40 °C ... 125 °C      |

#### General

|                      |  |
|----------------------|--|
| Note                 | For contact inserts HC-B10, BB18, DD42, M, K8/24 |
| Type                 | B10  |
| Housing type         | Box mounting bases                               |
| Locking type         | For double locking latch                         |
| No. of cable outlets | 2  |
| Cable exit           | Lateral  |

# Housing - HC-B 10-SFQD-52/M2PG16 - 1771419

## Technical data

### General

|                              |                     |
|------------------------------|---------------------|
| Screw connection             | with                |
| Type of the screw connection | 2x Pg16             |
| Protective cover             | Yes                 |
| Housing material             | Aluminum die-cast   |
| Housing surface material     | Powder-coated, gray |
| Seal material                | NBR                 |
| Cable gland material         | Nickel-plated brass |
| Cable seal material          | NBR                 |
| Material, protective cover   | Polyamide           |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27140816 |
| eCl@ss 4.1 | 27140816 |
| eCl@ss 5.0 | 27143424 |
| eCl@ss 5.1 | 27143424 |
| eCl@ss 6.0 | 27143424 |
| eCl@ss 7.0 | 27440209 |
| eCl@ss 8.0 | 27440202 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000437 |
| ETIM 3.0 | EC000437 |
| ETIM 4.0 | EC000437 |
| ETIM 5.0 | EC000437 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 31261502 |
| UNSPSC 7.0901 | 31261502 |
| UNSPSC 11     | 31261502 |
| UNSPSC 12.01  | 31261502 |
| UNSPSC 13.2   | 31261502 |

## Approvals

### Approvals

Approvals

EAC

# Housing - HC-B 10-SFQD-52/M2PG16 - 1771419

## Approvals

Ex Approvals

---

Approvals submitted

---

Approval details

|     |
|-----|
| EAC |
|-----|

## Drawings

Dimensioned drawing

