



Part Number : [368770006](#)
Product Description : Ditto Hermaphroditic Crimp Housing, Friction Lock, 6 Circuit, Natural
Series Number : 36877
Status : Obsolete
Product Category : Connector Housings



Documents & Resources

Drawings


[368770006 sd.pdf](#)
[368770006 stp.zip](#)

Specifications

[TS-36876-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Connector Housings
Series	36877
Description	Ditto Hermaphroditic Crimp Housing, Friction Lock, 6 Circuit, Natural
Application	Wire-to-Wire
Product Name	Ditto
UPC	887191584027

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	6
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Hermaphroditic
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.433/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm

Temperature Range - Operating	-40° to +105°C
-------------------------------	----------------

Mates With / Use With

Mates with Part(s)

Description	Part Number
Ditto Hermaphroditic Crimp Housings	<u>36877</u>

Use with Part(s)

Description	Part Number
Ditto Hermaphroditic Crimp Terminals	<u>36876</u>

This document was generated on Aug 04, 2025

Obsolète