

#### **FEATURES**

- 0.1db resolution.
- Back-screw for tripod fixture
- Micro-USB interface
- Back-screw for tripod fixture

# RS PRO Digital Sound Level Meter 8kHz

RS Stock No.: 146-4651



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



#### **Product Description**

The RS PRO RS-1151 is an 8KHz digital sound level meter. It has A, C, Z frequency weightings with measuring range from 30dB to 130dB. The meter offers AC and DC signal outputs from a single standard 3.5mm coaxial socket suitable for use with a frequency analyser, level recorder, FFT analyser, graphic recorder, etc. It has a 4 digits LCD with 0.1dB resolution. This device comes with 3.5φ plug, adjustment screwdriver, windscreen, CD software, micro-USB cable, a battery, an instruction manual, and a carrying case.

#### **General Specifications**

Sound Level Measurement Range	30dB-130dB RMS
Selectable ranges	30dB - 90dB, 45dB - 110dB, 65dB - 130dB
Microphone	1/2 inch Electret condenser microphone
Frequency Range	31.5Hz to 8kHz
Resolution	0.1dB
Frequency Weighting	A, C, Z
Time Weighting	Both
Output	1Vrms (at full-scale of the range) 10mV/dB
Display Type	LCD
Data Logging	Yes
Interface Type	Micro USB
Applicable Standards	IEC 61672-1: 2013 Class 2, ANSI S1.4: 1983 Type 2

#### **Electrical Specifications**

Power Source	One 006P 9V
Battery Type	NEDA 1604
Battery Life	Approx. 24 hours (1150) Approx. 7 hours (1151)



## **Mechanical Specifications**

Dimensions	246mm(L)×64mm(W)× 26mm (H)
Height	26mm
Width	64mm
Depth	246mm
Weight	Approx. 180g

### **Operation Environment Specifications**

Operating Humidity	90%RH non-condensing
Operating Temperature Range	-10°C to 50°C
Storage Temperature Range	-10°C to 60°C

## Approvals

Compliance/Certifications	RoHS









#### SPECIFICATIONS

SPECIFICATIONS	
Applicable standards	IEC 61672-1: 2013 Class 2, ANSI S1.4: 1983 Type 2
Display screens	4 digit numerical indication of sound level, from 30.0 to 130.0dB with 0.1dB resolution
Level range selection	30 - 90dB, 45 - 110dB, 65 - 130dB
Typical instrument frequency range	31.5Hz to 8kHz
Microphone	1/2 inch Electret condenser microphone
Data logger capacity	micro SD CARD 4GB (Maximum 99 blocks) (1151)
Warning indicator	OVER displayed at upper limit of the range UNDER displayed at lower limit of the range
AC output	1Vrms (at full-scale of the range)
DC output	10mV/dB
Operating temperature & humidity	-10°C to +50°C, 30% to 90%RH non-condensing
Storage temperature & humidity	-10°C to +60°C, <70%RH non-condensing
Power supply	One 006P 9V or IEC 6F22 or NEDA 1604 Battery
Battery life	Approx. 24 hours (1150) Approx. 7 hours (1151)
Dimensions	246(L)x64(W)x26(H)mm
Weight	Approx. 180g
Accessories	Instruction manual, Battery, Carrying case, 3.5¢ plug, Adjustment screwdriver, windscreen, CD Software (1151), micro-USB Cable (1151).
Optional accessory	AC adaptor DC9V 100mA (1151)