

AEACMK0660746-SG4



76.0 x Ø66.0 mm RoHS/RoHS II Compliant MSL = 1

Features

- Multiband GNSS antenna
- Covers GPS, GLONASS, BEIDOU, Galileo bands
- High Gain of 5dBic
- RHCP polarization
- Active GNSS with integrated LNA
- High LNA gain of 40 dB
- High positioning accuracy
- Screw Mounting

Applications

- GPS/GLONASS/BeiDou/Galileo applications
- IoT
- M2M
- Surveillance
- Fleet management and asset tracking
- Autonomous driving
- Telematics
- Agriculture
- Instrumentation
- Survey

Electrical Specifications

Parameters	Min.	Тур.	Max.	Units	Notes		
Antenna							
Center Frequency	1561		1602	MHz			
VSWR			1.5				
Gain		5		dBic	Zenith; Ground plane size: 100 mm		
Axial Ration		4		dB			
Impedance		50		Ω			
Polarization		RHCP					
LNA							
LNA Gain		40		dB			
Noise Figure			2.5	dB			
Ex-Band Attenuation		50		dB	$@$ CF \pm 50 MHz		
VSWR			2				
Supply Voltage	2.7		10	V	DC		
Current Consumption			25	mA			
Impedance		50		Ω			

Mechanical Specification

Parameters	Description	Notes
Connector	TNC (F)	
Radome Material	ABS	
Mounting Method	Screw / Body	





AEACMK0660746-SG4




76.0 x Ø66.0 mm RoHS/RoHS II Compliant MSL = 1

Environmental Specification

Parameters	Description	Notes
Operating Temperature	-40°C to +85°C	
Relative Humidity	Up to 95 %	
Ingress Protection	IP67	
Vibration	$10 \sim 55$ Hz with 1.5 mm amplitude 2 hours	
Shock	Vertical axis: 50G, Other axes: 30G	
ESD	15 KV	Air discharge

Product Dimension



Dimensions: mm







5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 11-4-20

ABRACON IS ISO9001-2015 CERTIFIED




AEACMK0660746-SG4



76.0 x Ø66.0 mm RoHS/RoHS II Compliant MSL = 1

VSWR








AEACMK0660746-SG4




76.0 x Ø66.0 mm RoHS/RoHS II Compliant MSL = 1

Radiation Pattern


2D Pattern



XZ Plane



YZ Plane



---- 1561 MHz

---- 1575 MHz

---- 1602 MHz





AEACMK0660746-SG4




76.0 x Ø66.0 mm RoHS/RoHS II Compliant MSL = 1


Radiation Pattern

3D Pattern






1575 MHz



1602 MHz







AEACMK0660746-SG4



76.0 x Ø66.0 mm RoHS/RoHS II Compliant MSL = 1

n			•
PЯ	CL	agi	mo
		uz	1112

A carton holds 50 pcs of antenna. Each carton is 38 x 38 x 19 cm and weighs 10 kg.

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

