

NC7NZ17

TinyLogic® UHS Triple Buffer with Schmitt Trigger Inputs

General Description

The NC7NZ17 is a triple buffer with Schmitt trigger inputs from Fairchild's Ultra High Speed Series of TinyLogic® in the US8 package. The device is fabricated with advanced CMOS technology to achieve ultra high speed with high output drive while maintaining low static power dissipation over a very broad V_{CC} operating range. The device is specified to operate over the 1.65V to 5.5V V_{CC} range. The inputs and outputs are high impedance when V_{CC} is 0V. Inputs tolerate voltages up to 7V independent of V_{CC} operating voltage. Schmitt trigger inputs typically achieve 1V hysteresis between the positive going and negative going input threshold voltage at 5V V_{CC} .

Features

- Space saving US8 surface mount package
- MicroPak™ Pb-Free leadless package
- Ultra High Speed: t_{PD} 3.6 ns Typ into 50 pF at 5V V_{CC}
- High Output Drive: ± 24 mA at 3V V_{CC}
- Broad V_{CC} Operating Range; 1.65V to 5.5V
- Power down high impedance inputs/outputs
- Overvoltage tolerant inputs facilitate 5V to 3V translation
- Proprietary noise/EMI reduction circuitry implemented

Ordering Code:


| Order Number | Package Number | Product Code Top Mark | Package Description | Supplied As |
|--------------|----------------|--------------------------|---|---------------------------|
| NC7NZ17K8X | MAB08A | NZ17 | 8-Lead US8, JEDEC MO-187, Variation CA 3.1mm Wide | 3k Units on Tape and Reel |
| NC7NZ17L8X | MAC08A | U4 | Pb-Free 8-Lead MicroPak, 1.6 mm Wide | 5k Units on Tape and Reel |

Pb-Free package per JEDEC J-STD-020B.

TinyLogic® is a registered trademark of Fairchild Semiconductor Corporation.
MicroPak™ is a trademark of Fairchild Semiconductor Corporation.

NC7NZ17 TinyLogic® UHS Triple Buffer with Schmitt Trigger Inputs

Logic Symbol



Pin Descriptions

| Pin Names | Description |
|--|-------------|
| A ₁ , A ₂ , A ₃ | Data Inputs |
| Y ₁ , Y ₂ , Y ₃ | Output |


Function Table

Y = A

| Input | Output |
|-------|--------|
| A | Y |
| L | L |
| H | H |


H = HIGH Logic Level L = LOW Logic Level

Connection Diagrams



(Top View)


Pin One Orientation Diagram



AAA represents Product Code Top Mark - see ordering code

Note: Orientation of Top Mark determines Pin One location. Read the Top Product Code Mark left to right, Pin One is the lower left pin (see diagram).

Pad Assignments for MicroPak



(Top Thru View)

Absolute Maximum Ratings (Note 1)

| | |
|--|-----------------|
| Supply Voltage (V_{CC}) | -0.5V to +7V |
| DC Input Voltage (V_{IN}) | -0.5V to +7V |
| DC Output Voltage (V_{OUT}) | -0.5V to +7V |
| DC Input Diode Current (I_{IK}) @ $V_{IN} < -0.5V$ | -50 mA |
| DC Output Diode Current (I_{OK}) @ $V_{OUT} < -0.5V$ | -50 mA |
| DC Output Current (I_{OUT}) | ±50 mA |
| DC V_{CC} /GND Current (I_{CC}/I_{GND}) | ±100 mA |
| Storage Temperature (T_{STG}) | -65°C to +150°C |
| Junction Temperature under Bias (T_J) | 150°C |
| Junction Lead Temperature (T_L) (Soldering, 10 seconds) | 260°C |
| Power Dissipation (P_D) @ +85°C | 250 mW |

Recommended Operating Conditions (Note 2)

| | |
|--|----------------|
| Supply Voltage Operating (V_{CC}) | 1.65V to 5.5V |
| Supply Voltage Data Retention (V_{CC}) | 1.5V to 5.5V |
| Input Voltage (V_{IN}) | 0V to 5.5V |
| Output Voltage (V_{OUT}) | 0V to V_{CC} |
| Operating Temperature (T_A) | -40°C to +85°C |
| Thermal Resistance (θ_{JA}) | 250°C/W |

Note 1: Absolute maximum ratings are DC values beyond which the device may be damaged or have its useful life impaired. The datasheet specifications should be met, without exception, to ensure that the system design is reliable over its power supply, temperature, and output/input loading variables. Fairchild does not recommend operation outside datasheet specifications.

Note 2: Unused inputs must be held HIGH or LOW. They may not float.

DC Electrical Characteristics

| Symbol | Parameter | V_{CC} (V) | $T_A = +25^\circ\text{C}$ | | | $T_A = -40^\circ\text{C to } +85^\circ\text{C}$ | | Units | Conditions | |
|-----------|----------------------------|-----------------|---------------------------|----------|------|---|------|-------|------------------------------|-----------------------------|
| | | | Min | Typ | Max | Min | Max | | | |
| V_P | Positive Threshold Voltage | 1.65 | 0.7 | 1.07 | 1.5 | 0.7 | 1.5 | V | | |
| | | 2.3 | 1.0 | 1.38 | 1.8 | 1.0 | 1.8 | | | |
| | | 3.0 | 1.3 | 1.74 | 2.2 | 1.3 | 2.2 | | | |
| | | 4.5 | 1.9 | 2.43 | 3.1 | 1.9 | 3.1 | | | |
| | | 5.5 | 2.2 | 2.88 | 3.6 | 2.2 | 3.6 | | | |
| V_N | Negative Threshold Voltage | 1.65 | 0.25 | 0.56 | 0.9 | 0.25 | 0.9 | V | | |
| | | 2.3 | 0.40 | 0.75 | 1.15 | 0.40 | 1.15 | | | |
| | | 3.0 | 0.6 | 0.98 | 1.5 | 0.6 | 1.5 | | | |
| | | 4.5 | 1.0 | 1.42 | 2.0 | 1.0 | 2.0 | | | |
| | | 5.5 | 1.2 | 1.68 | 2.3 | 1.2 | 2.3 | | | |
| V_H | Hysteresis Voltage | 1.65 | 0.15 | 0.51 | 1.0 | 0.15 | 1.0 | V | | |
| | | 2.3 | 0.25 | 0.62 | 1.1 | 0.25 | 1.1 | | | |
| | | 3.0 | 0.4 | 0.76 | 1.2 | 0.4 | 1.2 | | | |
| | | 4.5 | 0.6 | 1.01 | 1.5 | 0.6 | 1.5 | | | |
| | | 5.5 | 0.7 | 1.20 | 1.7 | 0.7 | 1.7 | | | |
| V_{OH} | HIGH Level Output Voltage | 1.65 | 1.55 | 1.65 | | 1.55 | | V | $V_{IN} = V_{IH}$ | $I_{OH} = -100 \mu\text{A}$ |
| | | 2.3 | 2.2 | 2.3 | | 2.2 | | | | |
| | | 3.0 | 2.9 | 3.0 | | 2.9 | | | | |
| | | 4.5 | 4.4 | 4.5 | | 4.4 | | | | |
| | | 1.65 | 1.29 | 1.52 | | 1.29 | | | | |
| | | 2.3 | 1.9 | 2.14 | | 1.9 | | | | |
| | | 3.0 | 2.4 | 2.75 | | 2.4 | | | | |
| | | 3.0 | 2.3 | 2.62 | | 2.3 | | | | |
| | | 4.5 | 3.8 | 4.13 | | 3.8 | | | | |
| | | V_{OL} | LOW Level Output Voltage | 1.65 | | 0.0 | 0.1 | | | 0.1 |
| 2.3 | | | | 0.0 | 0.1 | | 0.1 | | | |
| 3.0 | | | | 0.0 | 0.1 | | 0.1 | | | |
| 4.5 | | | | 0.0 | 0.1 | | 0.1 | | | |
| 1.65 | | | | 0.08 | 0.24 | | 0.24 | | | |
| 2.3 | | | | 0.10 | 0.3 | | 0.3 | | | |
| 3.0 | | | | 0.16 | 0.4 | | 0.4 | | | |
| 3.0 | | | | 0.24 | 0.55 | | 0.55 | | | |
| 4.5 | | | | 0.25 | 0.55 | | 0.55 | | | |
| I_{IN} | Input Leakage Current | | | 0 to 5.5 | | | ±0.1 | | ±1.0 | μA |
| I_{OFF} | Power Off Leakage Current | 0.0 | | | 1 | | 10 | μA | V_{IN} or $V_{OUT} = 5.5V$ | |

DC Electrical Characteristics (Continued)

| Symbol | Parameter | V _{CC} (V) | T _A = +25°C | | | T _A = -40°C to +85°C | | Units | Conditions |
|-----------------|--------------------------|------------------------|------------------------|-----|-----|---------------------------------|-----|-------|-----------------------------|
| | | | Min | Typ | Max | Min | Max | | |
| I _{CC} | Quiescent Supply Current | 1.65 to 5.5 | | | 1.0 | | 10 | μA | V _{IN} = 5.5V, GND |

AC Electrical Characteristics


| Symbol | Parameter | V _{CC} (V) | T _A = +25°C | | | T _A = -40°C to +85°C | | Units | Conditions | Figure Number |
|------------------|-------------------|------------------------|------------------------|-----|------|---------------------------------|------|-------|--|---------------|
| | | | Min | Typ | Max | Min | Max | | | |
| t _{PLH} | Propagation Delay | 1.8 ± 0.15 | 2.0 | 6.9 | 11.9 | 2.0 | 13.1 | ns | C _L = 15 pF, R _L = 1 MΩ | Figures 1, 3 |
| t _{PHL} | | 2.5 ± 0.2 | 1.5 | 4.8 | 8.2 | 1.5 | 9.0 | | | |
| | | 3.3 ± 0.3 | 1.0 | 3.7 | 5.6 | 1.0 | 6.2 | | | |
| | | 5.0 ± 0.5 | 0.8 | 3.0 | 4.7 | 0.8 | 5.2 | | | |
| t _{PLH} | Propagation Delay | 3.3 ± 0.3 | 1.5 | 4.3 | 6.6 | 1.5 | 7.3 | ns | C _L = 50 pF, R _L = 500Ω | Figures 1, 3 |
| t _{PHL} | | 5.0 ± 0.5 | 1.0 | 3.6 | 5.6 | 1.0 | 6.2 | | | |
| C _{IN} | Input Capacitance | 0 | 2.5 | | | | | pF | | |
| C _{PD} | Power Dissipation | 3.3 | 9 | | | | | pF | (Note 3) | Figure 2 |
| | Capacitance | 5.0 | 11 | | | | | | | |

Note 3: C_{PD} is defined as the value of the internal equivalent capacitance which is derived from dynamic operating current consumption (I_{CCD}) at no output loading and operating at 50% duty cycle. (See Figure 2.) C_{PD} is related to I_{CCD} dynamic operating current by the expression:
 $I_{CCD} = (C_{PD})(V_{CC})(f_{IN}) + (I_{CC} \text{static})$.

Dynamic Switching Characteristics


| Symbol | Parameter | Conditions | V _{CC} (V) | T _A = 25°C | Unit |
|------------------|---|---|------------------------|-----------------------|------|
| | | | | Typical | |
| V _{OLP} | Quiet Output Dynamic Peak V _{OL} | C _L = 50pF, V _{IH} = 5.0V, V _{IL} = 0V | 5.0 | 0.8 | V |
| V _{OLV} | Quiet Output Dynamic Valley V _{OL} | C _L = 50pF, V _{IH} = 5.0V, V _{IL} = 0V | 5.0 | -0.8 | V |

AC Loading and Waveforms



C_L includes load and stray capacitance
 Input PRR = 1.0 MHz; t_w = 500 ns

FIGURE 1. AC Test Circuit



Input = AC Waveform; t_r = t_f = 1.8 ns;
 PRR = variable; Duty Cycle = 50%

FIGURE 2. I_{CCD} Test Circuit





FIGURE 3. AC Waveforms



NC7NZ17

Tape and Reel Specification (Continued)
REEL DIMENSIONS inches (millimeters)






| Tape Size | A | B | C | D | N | W1 | W2 | W3 |
|-----------|----------------|-----------------|------------------|------------------|------------------|---|------------------|--|
| 8 mm | 7.0 (177.8) | 0.059 (1.50) | 0.512 (13.00) | 0.795 (20.20) | 2.165 (55.00) | 0.331 + 0.059/-0.000 (8.40 + 1.50/-0.00) | 0.567 (14.40) | W1 + 0.078/-0.039 (W1 + 2.00/-1.00) |

Physical Dimensions inches (millimeters) unless otherwise noted



LAND PATTERN RECOMMENDATION



DETAIL A


NOTES:

- A. CONFORMS TO JEDEC REGISTRATION MO-187
- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
- D. DIMENSIONS AND TOLERANCES PER ANSI Y14.5M, 1982.

MAB08AREVC

**8-Lead US8, JEDEC MO-187, Variation CA 3.1mm Wide
Package Number MAB08A**

Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



Notes:

1. PACKAGE CONFORMS TO JEDEC MO-255 VARIATION UAAD
2. DIMENSIONS ARE IN MILLIMETERS
3. DRAWING CONFORMS TO ASME Y.14M-1994
4. PIN 1 FLAG, END OF PACKAGE OFFSET.

MAC08AREVC

**Pb-Free 8-Lead MicroPak, 1.6 mm Wide
Package Number MAC08A**

Fairchild does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and Fairchild reserves the right at any time without notice to change said circuitry and specifications.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

www.fairchildsemi.com