



SAFETY DATA SHEET

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Trade name or designation of the mixture	Aqua Gel II
Registration number	-
Synonyms	None.
Product code	31-378 / 31-371 / 31-375 / 31-3855
Issue date	14-June-2019
Version number	01
Revision date	-
Supersedes date	-

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Wire/Cable Pulling Lubricant.
Uses advised against	None known.

1.3. Details of the supplier of the safety data sheet

Manufacturer/Supplier	IDEAL INDUSTRIES Limited Unit 3, Europa Court Europa Boulevard, Warrington Cheshire, WA5 7TN United Kingdom
Telephone number	+44 (0)1925 444446
e-mail	reach@idealnwd.com
1.4. Emergency telephone number	In England and Wales (NHS Direct): 0845 4647 In Scotland (NHS 24): 08454 242424

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

The mixture has been assessed and/or tested for its physical, health and environmental hazards and the following classification applies.

Classification according to Regulation (EC) No 1272/2008 as amended

This mixture does not meet the criteria for classification according to Regulation (EC) 1272/2008 as amended.

Hazard summary Not classified for health hazards. However, occupational exposure to the mixture or substance(s) may cause adverse health effects.

2.2. Label elements

Label according to Regulation (EC) No. 1272/2008 as amended

Hazard pictograms	None.
Signal word	None.
Hazard statements	The mixture does not meet the criteria for classification.

Precautionary statements

Prevention	Observe good industrial hygiene practices.
Response	Wash hands after handling.
Storage	Store away from incompatible materials.
Disposal	Dispose of waste and residues in accordance with local authority requirements.

Supplemental label information None.

2.3. Other hazards This mixture does not contain substances assessed to be vPvB / PBT according to Regulation (EC) No 1907/2006, Annex XIII.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

General information

Chemical name	%	CAS-No. / EC No.	REACH Registration No.	Index No.	Notes
20% Potassium Hydroxide	< 2	1310-58-3 215-181-3	-	019-002-00-8	
Classification:	Acute Tox. 4;H302, Skin Corr. 1A;H314				
Bronopol	< 0.1	52-51-7 200-143-0	-	603-085-00-8	
Classification:	Acute Tox. 4;H302, Acute Tox. 4;H312, Skin Irrit. 2;H315, Eye Dam. 1;H318, STOT SE 3;H335, Aquatic Acute 1;H400(M=10)				

List of abbreviations and symbols that may be used above

Components not listed are either non-hazardous or are below reportable limits.

Composition comments All concentrations are in percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume. The full text for all H-statements is displayed in section 16.

SECTION 4: First aid measures

General information Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

4.1. Description of first aid measures

Inhalation Move to fresh air. Call a physician if symptoms develop or persist.

Skin contact Wash off with soap and water. Get medical attention if irritation develops and persists.

Eye contact Flush eyes thoroughly with water for at least 15 minutes. Get medical attention if irritation develops and persists.

Ingestion Rinse mouth. Do not induce vomiting. Get medical attention if symptoms occur.

4.2. Most important symptoms and effects, both acute and delayed Exposure may cause temporary irritation, redness, or discomfort.

4.3. Indication of any immediate medical attention and special treatment needed Treat symptomatically.

SECTION 5: Firefighting measures

General fire hazards No unusual fire or explosion hazards noted.

5.1. Extinguishing media

Suitable extinguishing media Use fire-extinguishing media appropriate for surrounding materials.

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture During fire, gases hazardous to health may be formed.

5.3. Advice for firefighters

Special protective equipment for firefighters Self-contained breathing apparatus and full protective clothing must be worn in case of fire.

Special fire fighting procedures Move containers from fire area if you can do so without risk.

Specific methods Use standard firefighting procedures and consider the hazards of other involved materials.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel Keep unnecessary personnel away. Avoid prolonged and repeated contact.

For emergency responders Use personal protection recommended in Section 8 of the SDS.

6.2. Environmental precautions Avoid discharge into drains, water courses or onto the ground.

6.3. Methods and material for containment and cleaning up Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. In case of spills, beware of slippery floors and surfaces. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water.

Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.

Never return spills to original containers for re-use.

6.4. Reference to other sections For personal protection, see section 8 of the SDS. For waste disposal, see section 13 of the SDS.

SECTION 7: Handling and storage

7.1. Precautions for safe handling	Avoid prolonged exposure. Avoid contact with skin and eyes. Be aware of potential for surfaces to become slippery. Ensure adequate ventilation. Wear personal protective equipment. Observe good industrial hygiene practices.
7.2. Conditions for safe storage, including any incompatibilities	Store in tightly closed container. Protect from freezing. Store at temperatures between 4°C and 82°C. Store away from incompatible materials (see section 10 of the SDS).
7.3. Specific end use(s)	Wire/Cable Pulling Lubricant.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

UK. EH40 Workplace Exposure Limits (WELs)

Components	Type	Value
20% Potassium Hydroxide (CAS 1310-58-3)	STEL	2 mg/m3

Biological limit values No biological exposure limits noted for the ingredient(s).

Recommended monitoring procedures Follow standard monitoring procedures.

Derived no effect levels (DNELs) Not available.

Predicted no effect concentrations (PNECs) Not available.

8.2. Exposure controls

Appropriate engineering controls Good general ventilation should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Individual protection measures, such as personal protective equipment

General information Personal protection equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment.

Eye/face protection Not normally needed. If risk of splashing, wear safety goggles or face shield.

Skin protection

- Hand protection Not normally needed. Protective gloves should be used if there is a risk of direct contact or splash. Neoprene gloves are recommended.

- Other No skin protection is ordinarily required under normal conditions of use. In accordance with good industrial hygiene practices, precautions should be taken to avoid skin contact.

Respiratory protection No personal respiratory protective equipment normally required.

Thermal hazards Wear appropriate thermal protective clothing, when necessary.

Hygiene measures Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

Environmental exposure controls Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. Fume scrubbers, filters or engineering modifications to the process equipment may be necessary to reduce emissions to acceptable levels.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance

Physical state Liquid.

Form Gel.

Colour Blue.

Odour Mild odor.

Odour threshold Not available.

pH 6.5 - 8

Melting point/freezing point Not available.

Initial boiling point and boiling range 100 °C (212 °F)

Flash point None.

Evaporation rate	Not available.
Flammability (solid, gas)	Not applicable.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Vapour pressure	Not available.
Vapour density	Not available.
Relative density	0.993 - 1.033
Solubility(ies)	Soluble.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	20000 - 40000 cps
Explosive properties	Not explosive.
Oxidising properties	Not oxidising.
9.2. Other information	
Percent volatile	< 90 %

SECTION 10: Stability and reactivity

10.1. Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
10.2. Chemical stability	Material is stable under normal conditions.
10.3. Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use. Nitrosamines, many of which are known to be potent carcinogens, may be formed when the product comes in contact with nitrites.
10.4. Conditions to avoid	Strong heating. Contact with incompatible materials.
10.5. Incompatible materials	Strong oxidising agents. Nitrites.
10.6. Hazardous decomposition products	Nitrogen oxides. Carbon monoxide. Carbon dioxide.

SECTION 11: Toxicological information

General information	Occupational exposure to the substance or mixture may cause adverse effects.
Information on likely routes of exposure	
Inhalation	Prolonged inhalation may be harmful.
Skin contact	No adverse effects due to skin contact are expected.
Eye contact	No adverse effects due to eye contact are expected.
Ingestion	May cause discomfort if swallowed. However, ingestion is not likely to be a primary route of occupational exposure.
Symptoms	Exposure may cause temporary irritation, redness, or discomfort.

11.1. Information on toxicological effects

Acute toxicity Not expected to be acutely toxic.

Components	Species	Test Results
20% Potassium Hydroxide (CAS 1310-58-3)		
<u>Acute</u>		
Oral		
LD50	Rat	273 mg/kg
Skin corrosion/irritation	Based on available data, the classification criteria are not met.	
Serious eye damage/eye irritation	Based on available data, the classification criteria are not met.	
Respiratory sensitisation	Due to partial or complete lack of data the classification is not possible.	
Skin sensitisation	Due to partial or complete lack of data the classification is not possible.	
Germ cell mutagenicity	Due to partial or complete lack of data the classification is not possible.	
Carcinogenicity	Due to partial or complete lack of data the classification is not possible.	
Reproductive toxicity	Due to partial or complete lack of data the classification is not possible.	

Specific target organ toxicity - single exposure	Due to partial or complete lack of data the classification is not possible.
Specific target organ toxicity - repeated exposure	Due to partial or complete lack of data the classification is not possible.
Aspiration hazard	Based on available data, the classification criteria are not met.
Mixture versus substance information	No information available.
Other information	No other specific acute or chronic health impact noted.

SECTION 12: Ecological information

12.1. Toxicity	The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.
12.2. Persistence and degradability	No data is available on the degradability of any ingredients in the mixture.
12.3. Bioaccumulative potential	No data available on bioaccumulation.
Bioconcentration factor (BCF)	Not available.
12.4. Mobility in soil	The product is soluble in water.
12.5. Results of PBT and vPvB assessment	This mixture does not contain substances assessed to be vPvB / PBT according to Regulation (EC) No 1907/2006, Annex XIII.
12.6. Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

SECTION 13: Disposal considerations

13.1. Waste treatment methods	
Residual waste	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.
EU waste code	The Waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Disposal methods/information	Collect and reclaim or dispose in sealed containers at licensed waste disposal site.
Special precautions	Dispose in accordance with all applicable regulations.

SECTION 14: Transport information

ADR

14.1. - 14.6.: Not regulated as dangerous goods.

RID

14.1. - 14.6.: Not regulated as dangerous goods.

ADN

14.1. - 14.6.: Not regulated as dangerous goods.

IATA

14.1. - 14.6.: Not regulated as dangerous goods.

IMDG

14.1. - 14.6.: Not regulated as dangerous goods.

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not established.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU regulations

Regulation (EC) No. 1005/2009 on substances that deplete the ozone layer, Annex I and II, as amended
Not listed.

Regulation (EC) No. 850/2004 On persistent organic pollutants, Annex I as amended
Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 1 as amended
Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 2 as amended
Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 3 as amended
Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex V as amended
Not listed.

Regulation (EC) No. 166/2006 Annex II Pollutant Release and Transfer Registry, as amended
Not listed.

Regulation (EC) No. 1907/2006, REACH Article 59(10) Candidate List as currently published by ECHA
Not listed.

Authorisations

Regulation (EC) No. 1907/2006, REACH Annex XIV Substances subject to authorization, as amended
Not listed.

Restrictions on use

Regulation (EC) No. 1907/2006, REACH Annex XVII Substances subject to restriction on marketing and use as amended
Not listed.

Directive 2004/37/EC: on the protection of workers from the risks related to exposure to carcinogens and mutagens at work, as amended.
Not listed.

Other EU regulations

Directive 2012/18/EU on major accident hazards involving dangerous substances, as amended
Not listed.

Other regulations

The product is classified and labelled in accordance with Regulation (EC) 1272/2008 (CLP Regulation) as amended. This Safety Data Sheet complies with the requirements of Regulation (EC) No 1907/2006, as amended.

National regulations

Follow national regulation for work with chemical agents in accordance with Directive 98/24/EC, as amended.

15.2. Chemical safety assessment

No Chemical Safety Assessment has been carried out.

SECTION 16: Other information

List of abbreviations

LD50: Lethal Dose, 50%.
PBT: Persistent, bioaccumulative, toxic.
vPvB: very Persistent, very Bioaccumulative.

References

ECHA: European Chemical Agency.
IARC Monographs. Overall Evaluation of Carcinogenicity

Information on evaluation method leading to the classification of mixture

The classification for health and environmental hazards is derived by a combination of calculation methods and test data, if available.

Full text of any H-statements not written out in full under Sections 2 to 15

H302 Harmful if swallowed.
H312 Harmful in contact with skin.
H314 Causes severe skin burns and eye damage.
H315 Causes skin irritation.
H318 Causes serious eye damage.
H335 May cause respiratory irritation.
H400 Very toxic to aquatic life.

Training information

Follow training instructions when handling this material.

Disclaimer

IDEAL INDUSTRIES cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information in the sheet was written based on the best knowledge and experience currently available.