

# Product datasheet

Specifications



switch disconnector, Compact  
INS630 , 630 A, standard version  
with black rotary handle, 3 poles

Local distributor code:  
382087330 31114

EAN Code: 3303430311140

## Main

Range	ComPact
Product or component type	Switch disconnector
product name	ComPacT INS
Poles description	3P
Network type	AC DC
Network frequency	50/60 Hz
[Ie] rated operational current	AC-22A: 630 A AC 50/60 Hz 220/240 V AC-22A: 630 A AC 50/60 Hz 380/415 V AC-22A: 630 A AC 50/60 Hz 440/480 V AC-22A: 630 A AC 50/60 Hz 480 V NEMA AC-22A: 630 A AC 50/60 Hz 500/525 V AC-22A: 630 A AC 50/60 Hz 660/690 V AC-23A: 630 A AC 50/60 Hz 220/240 V AC-23A: 630 A AC 50/60 Hz 380/415 V AC-23A: 630 A AC 50/60 Hz 440/480 V AC-23A: 630 A AC 50/60 Hz 480 V NEMA AC-23A: 630 A AC 50/60 Hz 500/525 V AC-23A: 630 A AC 50/60 Hz 660/690 V DC-22A: 550 A DC 125 V 2 poles in series DC-23A: 550 A DC 125 V 2 poles in series DC-23B: 630 A DC 125 V 2 poles in series
[Ui] rated insulation voltage	800 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV 8 kV conforming to IEC 60947-3
[Ith] conventional free air thermal current	630 A at 60 °C
[Icm] rated short-circuit making capacity	330 kA with upstream protection circuit breaker 690 V AC at 50/60 Hz 50 kA switch-disconnector alone 690 V AC at 50/60 Hz
[Ue] rated operational voltage	125 V DC 690 V AC 50/60 Hz
Suitability for isolation	Yes
Contact position indicator	Yes
Visible break	No
Pollution degree	3

## Complementary

control type	Direct front rotary handle
Handle colour	Black
Mounting mode	Fixed

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mounting support	Rail Plate
Upside connection	Front
Downside connection	Front
Maximum power	AC-23: 200 kW at 220/240 V AC 50/60 Hz AC-23: 200 kW at 230 V AC 50/60 Hz (NEMA) AC-23: 315 kW at 380/415 V AC 50/60 Hz AC-23: 375 kW at 480 V AC 50/60 Hz (NEMA) AC-23: 400 kW at 440 V AC 50/60 Hz AC-23: 400 kW at 500/525 V AC 50/60 Hz AC-23: 560 kW at 660/690 V AC 50/60 Hz
Rated duty	Uninterrupted
[Icw] rated short-time withstand current	11.5 kA during 3 s conforming to IEC 60947-3 20 kA during 1 s conforming to IEC 60947-3 4 kA during 30 s conforming to IEC 60947-3 4.9 kA during 20 s conforming to IEC 60947-3
Mechanical durability	10000 cycles
Electrical durability	AC-22A: 1500 cycles 440 V AC 50/60 Hz AC-22A: 1500 cycles 500 V AC 50/60 Hz AC-22A: 1500 cycles 690 V AC 50/60 Hz AC-23A: 1500 cycles 440 V AC 50/60 Hz AC-23A: 1500 cycles 500 V AC 50/60 Hz AC-23A: 1500 cycles 690 V AC 50/60 Hz DC-23A: 1000 cycles 125 V DC 2 poles in series DC-23B: 200 cycles 125 V DC 2 poles in series
Connection pitch	45 mm
Height	205 mm
Width	185 mm
Depth	120 mm
Net weight	4.6 kg

## Environment

Standards	IEC 60947-3 IEC 60947-1
Product certifications	CCC KEMA-KEUR
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	19.200 cm
Package 1 Width	19.200 cm
Package 1 Length	22.400 cm
Package 1 Weight	5.000 kg
Unit Type of Package 2	S04
Number of Units in Package 2	4

Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	20.701 kg
Unit Type of Package 3	P12
Number of Units in Package 3	16
Package 3 Height	50.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	94.003 kg

## Logistical informations

Country of origin	PL
-------------------	----

## Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)


[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	866
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
<a href="#">EU RoHS Directive</a>	Compliant with Exemptions
SCIP Number	Bbc62998-8aa6-42dc-8088-17a5c936153d
REACH Regulation	<a href="#">REACH Declaration</a>

Use Again

Repack and remanufacture	
Circularity Profile	<a href="#">End of Life Information</a>
Take-back	No
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins