

SAC-4P-MR/ 5,0-PUR/FR SCO - Sensor/actuator cable

1538296
<https://www.phoenixcontact.com/gb/products/1538296>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PUR halogen-free, black-gray RAL 7021, Plug angled M12 SPEEDCON, coding: A, on Socket angled M12 SPEEDCON, coding: A, cable length: 5 m

Commercial data

Item number	1538296
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AF1CCA
Product key	AF1CCA
GTIN	4046356075220
Weight per piece (including packing)	147 g
Weight per piece (excluding packing)	147 g
Customs tariff number	85444290
Country of origin	PL

SAC-4P-MR/ 5,0-PUR/FR SCO - Sensor/actuator cable



1538296

<https://www.phoenixcontact.com/gb/products/1538296>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	4
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	250 V AC
	250 V DC
Nominal current I_N	4 A

Signaling

Status display	no
Status display present	no

Connection data

Conductor connection

Tightening torque	0.4 Nm
-------------------	--------

Connector

Connection 1

Type	Plug angled M12 SPEEDCON
Number of positions	4
Locking type	SPEEDCON
Coding type	A

Connection 2

SAC-4P-MR/ 5,0-PUR/FR SCO - Sensor/actuator cable

1538296


<https://www.phoenixcontact.com/gb/products/1538296>

Type	Socket angled M12 SPEEDCON
Number of positions	4
Locking type	SPEEDCON
Coding type	A

Cable/line

Cable length	5 m
--------------	-----

PUR halogen-free black [PUR]

Dimensional drawing	
Cable weight	30 kg/km
UL AWM Style	20549 / 10493 (80°C/300 V)
Number of positions	4
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross section	4x 0.34 mm² (Signal line)
Wire diameter incl. insulation	1.27 mm ±0.02 mm
External cable diameter	4.20 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, white, blue, black
Thickness, insulation	≥ 0.21 mm
Thickness, outer sheath	approx. 0.50 mm
Overall twist	4 wires, twisted
Max. conductor resistance	≤ 58 Ω/km
Insulation resistance	≥ 1 GΩ*km
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	21 mm
Smallest bending radius, movable installation	42 mm
Dynamic load capacity (bending)	Max. bending cycles: 10000000, Bending radius: 42 mm,

SAC-4P-MR/ 5,0-PUR/FR SCO - Sensor/actuator cable



1538296

<https://www.phoenixcontact.com/gb/products/1538296>

	Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s ²
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: ≥2000000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815
	in accordance with DIN EN 50267-2-1
Flame resistance	in accordance with UL 758/1581 FT2
	DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Highly resistant to acids, alkaline solutions and solvents
	hydrolysis and microbe resistant
	partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
	Low adhesion
	abrasion-resistant
Special properties	Flexible cable conduit capable
	Silicone-free
	Free of substances which would hinder coating with paint or varnish
	flexible
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-25 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)


SAC-4P-MR/ 5,0-PUR/FR SCO - Sensor/actuator cable

1538296

<https://www.phoenixcontact.com/gb/products/1538296>


Drawings

Dimensional drawing



M12 x 1 male plug, angled

Dimensional drawing




M12 x 1 socket, angled

SAC-4P-MR/ 5,0-PUR/FR SCO - Sensor/actuator cable

1538296

<https://www.phoenixcontact.com/gb/products/1538296>

Schematic diagram




Pin assignment M12 plug, 4-pos., A-coded, view plug side

SAC-4P-MR/ 5,0-PUR/FR SCO - Sensor/actuator cable

1538296


<https://www.phoenixcontact.com/gb/products/1538296>

Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

Circuit diagram



SAC-4P-MR/ 5,0-PUR/FR SCO - Sensor/actuator cable



1538296
<https://www.phoenixcontact.com/gb/products/1538296>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1538296>

	UL Listed Approval ID: FILE E 221474			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	300 V	4 A	-	-

	cUL Listed Approval ID: FILE E 221474			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	300 V	4 A	-	-

	EAC-RoHS Approval ID: RU D-DE.HB35.B.00387			

SAC-4P-MR/ 5,0-PUR/FR SCO - Sensor/actuator cable



1538296
<https://www.phoenixcontact.com/gb/products/1538296>

Classifications

ECLASS

ECLASS-13.0	27060311
-------------	----------

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-4P-MR/ 5,0-PUR/FR SCO - Sensor/actuator cable



1538296
<https://www.phoenixcontact.com/gb/products/1538296>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk