

COAXIAL CONNECTOR, BMA, 50 Ohm, Straight bulkhead cable plug (male)

14_BMA-50-2-3/199_N

Properties

- Offers a range of floating configurations
- High reliability and ease of assembly
- Intermatable with the OSP connectors series
- Applicable in frequencies up to 18 GHz



Product configuration		
Interface type	Gender	Standard
BMA	plug	IEC 60169-33_MIL-STD-348A/321

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer conductor	Stainless steel	
Body	Stainless steel	
Insulator	PFA / PTFE	
Fastening nut	Stainless steel	
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper	Nickel Plating

Electrical data	
Impedance	50 Ω
Interface frequency	18 GHz

Mechanical data	
Weight	0.0035 kg
Mating cycles	1000
Cable entry centre contact	soldered
Cable entry outer contact	crimped

Engagement / Disengagement force		
	Engagement	Disengagement
Interface force min		2 N
Interface force max	14 N	

COAXIAL CONNECTOR, BMA, 50 Ohm, Straight bulkhead cable plug (male)

14_BMA-50-2-3/199_N

Environmental data	
Operation temperature	-65 °C ... 125 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22645614	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22645614	14_BMA-50-2-3/199_NE	Single

Suitable cables	
Cable group	U2 - 2 mm / 50 Ohm
Suitable cables	RG_316_/U
	RG_188_A/U
	RG_174_/U

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22544715	74_Z-0-0-68	Knives / Blades

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3196 / Date of publication: 12.07.2025 / uncontrolled copy