

## TECHNICAL DATA SHEET

# PROFESSIONAL FLUORESCENT TRACER PAINT

## *Enamel spray paint for manual tracing*

### - PRODUCT DESCRIPTION

Rapid-drying enamel spray paint for manual tracing on walls, floors, asphalt, cement and wood. Its high quality acrylic resin enables excellent adhesion to most materials, the special pigments also ensure high, long-lasting coverage on surfaces subject to rubbing, repeated friction or continuously exposed to the weather. The fluorescent finish gives the product excellent visibility, even in low light conditions.

### - FIELDS OF USE

The high quality and ease of application enable both construction sites and private use for a wide range of requirements: marking out danger zones, making reference points visible for excavation works, applications in the building, naval, agricultural and industrial sectors. The dispenser button is designed to produce a constant spray and enables lines to be traced precisely and evenly.

The product can be used in all positions thanks to the special "360°" valve.

### - TECHNICAL SPECIFICATIONS

• Appearance	Liquid
• Color	various
• Odor	Typical
• Pressure	3.5 bar
• Flash point	-1°C

The reported data are subject to normal manufacturing tolerances.

### - METHOD OF USE

Shake the can vigorously for at least two minutes until the balls inside are moving freely. Ensure the surface to be treated is dry and free of dirt. Spray from a distance of 20-30 cm.

The product dries in 5-10 minutes depending on the temperature and the quantity of product sprayed. Thanks to the self-cleaning valve, the usual cleaning operation for sprays with standard valves with the bottle turned upside down is not required.

### - STORAGE

Unopened and stored at room temperature, for at least 3 years

### - PACKAGING

500 ml spray can

Code 2775 Fluorescent orange

Code 2776 Fluorescent red

Code 2777 Fluorescent yellow

Code 2778 Fluorescent green

Code 2779 Fluorescent blue

### - ADDITIONAL INFORMATION

For further information about product safety, please consult Material Safety Data Sheet.

R&D 17.12.2024

The data contained herein are the result of technological research by our laboratories and are given for informative purposes only. We exclude any liability deriving from the incorrect choice or application of the product and from the lack of the necessary precautions, which should be carefully checked by the user. For information, please contact our Technical Dept. on no. +39 02924361

#### AREXONS S.p.A. A SOCIO UNICO

Via Antica di Cassano, 23

20063 Cernusco sul Naviglio (MI) Italy

Capitale Sociale: € 15.000.000,00 I.V.

Registro delle Imprese di Milano n. 09728360968

Codice Fiscale e Partita IVA 09728360968

Direzione e coordinamento ex art. 2497 c.c. PLI (Netherlands) B.V.

Centralino 02 92436.1

Fax 02 92436.306

[www.arexons.com](http://www.arexons.com)

A wholly-owned subsidiary of PETRONAS

Sistemi di gestione di qualità della società Arexons S.p.A.  
certificati ISO 9001 da LRQA.

Sistemi di gestione di ambiente e sicurezza della società Arexons S.p.A.  
certificati ISO 14001 e OHSAS 18001 da Bureau Veritas.

