

# ZB5AVBG4

Light block with body fixing collar, Harmony XB5, plastic, red, integral LED, 24...120V AC DC



Important message: All colored LED are replaced with a single Universal LED block for use with new illuminated heads (more information at [se.com/harmonyxb4](http://se.com/harmonyxb4) or [se.com/harmonyxb5](http://se.com/harmonyxb5))



## Commercial status

End-of-Sale Notice : JAN 13, 2023

⚠ End-of-Sale Notice

## Main

Range of product	Harmony XB5
Product or component type	Complete body/light block assembly
Device short name	ZB5
Fixing collar material	Plastic
Sale per indivisible quantity	1
Connections - terminals	Screw clamp terminals, $\leq 2 \times 1.5 \text{ mm}^2$ with cable end conforming to EN 60947-1 Screw clamp terminals, $\geq 1 \times 0.22 \text{ mm}^2$ without cable end conforming- to EN 60947-1
Light source	Protected LED
Bulb base	Integral LED
Light source colour	Red

## Complementary

CAD overall width	30 Mm
CAD overall height	42 Mm
CAD overall depth	32 Mm
Terminals description ISO n°1	(X1-X2)PL
Net weight	0.022 Kg
Tightening torque	0.8...1.2 N.M conforming to EN 60947-1
Shape of screw head	Cross compatible with Philips no 1 screwdriver Cross compatible with pozidriv No 1 screwdriver Slotted compatible with flat Ø 4 mm screwdriver Slotted compatible with flat Ø 5.5 mm screwdriver
[Ui] rated insulation voltage	600 V (pollution degree 3) conforming to EN 60947-1
[Uimp] rated impulse withstand voltage	6 KV conforming to EN 60947-1
Signalling type	Steady
[Us] rated supply voltage	24...120 V AC/DC at 50/60 Hz
Supply voltage limits	19.2...132 V DC 21.6...132 V AC
Service life	100000 H at rated voltage and 25 °C

Surge withstand	1 KV conforming to IEC 61000-4-5
Device presentation	Basic sub-assemblies



## Environment

Protective treatment	TH
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-40...70 °C
Electrical shock protection class	Class II conforming to IEC 60536
Standards	EN/IEC 60947-5-1 EN/IEC 60947-1 CSA C22.2 No 14 EN/IEC 60947-5-4 UL 508 JIS C8201-5-1 JIS C8201-1
Product certifications	LROS (Lloyds register of shipping) BV GL CSA DNV UL listed
Vibration resistance	5 gn (f= 2...500 Hz) conforming to IEC 60068-2-6
Shock resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming- to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming- to IEC 60068-2-27
Resistance to fast transients	2 KV conforming to IEC 61000-4-4
Resistance to electromagnetic fields	10 V/M conforming to IEC 61000-4-3
Resistance to electrostatic discharge	6 KV on contact (on metal parts) conforming to IEC 61000-2-6 8 KV in free air (in insulating parts) conforming to IEC 61000-2-6
Electromagnetic emission	Class B conforming to IEC 55011

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.6 Cm
Package 1 Width	3.4 Cm
Package 1 Length	5.4 Cm
Package 1 Weight	20 G
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	4.5 Cm
Package 2 Width	3.5 Cm
Package 2 Length	26.5 Cm
Package 2 Weight	100 G
Unit Type of Package 3	S02
Number of Units in Package 3	100
Package 3 Height	15 Cm
Package 3 Width	30 Cm
Package 3 Length	40 Cm
Package 3 Weight	2.303 Kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes

China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and-lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

### Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status :	End of commercialisation
-----------------------	--------------------------

ZB5AVBG4 may be replaced by any of the following products:



#### ZB5AVBG1

Complete body/light block assembly, Harmony XB5, plastic, universal LED, body/fixing collar, 24...120V AC DC

Qty 1

Substitution date: |