

SOFT TOUCH CONTROL PANEL FOR OPERATING WELDING THICKNESS & TIMER FUNCTION (MAX. THICKNESS 1.5MM - 1.5MM)



FITTED WITH A HEAVY-DUTY WELD SWITCH FOR RELIABLE OPERATION




OPERATES FROM A 13A SUPPLY FOR EASE-OF-USE



HEAVY-DUTY CARRY HANDLE FOR WORK AREA MOVEMENT



SUPPLIED WITH REPLACEMENT 16MM COPPER/CHROME ELECTRODES



AVAILABLE WITH ADDITIONAL ELECTRODES & BODYWORK KIT

ITEM. 25298

SIP WELDMATE® PRO SW150 SPOT WELDER WITH TIMER

PORTABLE SPOT WELDER WITH TIMER FOR CONSISTENT WELDS

PRODUCT OVERVIEW

The **SIP WELDMATE® PRO SW150 Spot Welder with Timer** is a portable resistance welder designed for sheet metal applications in automotive environments and light fabrication workshops.

Ideal for vehicle body panel repairs and light sheet metal tasks, this easy-to-use welder uses copper/chrome alloy electrodes to achieve a maximum welding thickness of 1.5mm - 1.5mm and features a microprocessor-controlled timer function for precise and consistent welds.

For added flexibility the welder operates from a 13A supply. It is also available with a range of additional electrode arms sold individually or as a bodywork kit for greater application versatility.

FEATURES & BENEFITS

✓ INTUITIVE SOFT TOUCH CONTROL PANEL FEATURES ADJUSTABLE WELDING THICKNESS & TIMER FUNCTION FOR ROBUST & REPEATABLE WELDING CAPABILITY IN A VARIETY OF APPLICATIONS

Maximum welding thickness of 1.5mm - 1.5mm with sufficient welding current output to achieve 3 welds per minute.

A microprocessor-controlled timer function allows settings of 120~900ms for consistent welds.

Offers strong localised welds with minimal heat distortion to the surrounding sheet metal.

Suitable for mild steel, stainless steel and galvanised steel.

Handle allows for easy alignment of the electrodes for accurate welding performance.

Fitted with a heavy-duty weld switch for reliable operation in demanding environments.

Supplied with a set of replacement 16mm copper/chrome electrodes.

THIS PRODUCT COMES WITH AN SIP 2-YEAR SILVER WARRANTY*

FIND OUT MORE AT SIP-GROUP.COM/WARRANTY



ITEM. 25298

SIP WELDMATE® PRO SW150 SPOT WELDER WITH TIMER

FEATURES & BENEFITS CONT.

ADDITIONAL ELECTRODES & BODYWORK KITS AVAILABLE FOR GREATER APPLICATION VERSATILITY

These easy-to-fit accessories are sold separately as individual parts or available as a bodywork kit.
 The 16mm electrode arms offer added dexterity for a variety of welding applications.

- 25418 SIP Spot Welder 120mm Arms with Straight Electrodes (ø 16mm)
- 25417 SIP Spot Welder 120mm Arms with Offset Electrodes (ø 16mm)
- 25419 SIP Spot Welder 350mm Arms with Offset Electrodes (ø 16mm)
- 25415 SIP Spot Welder 350mm Restricted Access Arms with Offset Electrodes (ø 16mm)
- 25416 SIP Spot Welder 120mm Arms with Swan Neck Electrodes (ø 16mm)
- 25424 SIP Spot Welder 5pc Bodywork Kit (ø 16mm) (for 25298)

WHAT'S IN THE BOX?

- 1x SIP WELDMATE® PRO SW150 Spot Welder with Timer
- 2x 16mm straight electrodes
- 1x steel carry handle with 4x fixing screws
- User manual available via QR code sticker applied to product

APPLICATIONS & USES

PERFECT FOR AUTOMOTIVE & GARAGE ENVIRONMENTS

IDEAL FOR SHEET METAL WELDING APPLICATIONS

SUITABLE FOR FABRICATION WORKSHOPS

SUITABLE FOR MILD STEEL, STAINLESS STEEL & GALVANISED STEEL

ITEM NO.	25298
INPUT SUPPLY	230v (13A)
MAX. WELDING THICKNESS	1.5mm - 1.5mm
SPOT DURATION	120~900ms
WELDS PER MINUTE	3 welds per minute
MAX. ELECTRODE FORCE	460N
NET WEIGHT	12.6kg
GROSS WEIGHT	13.5kg
PRODUCT DIMENSIONS	244(H) x 94(W) x 475mm(D)
PACKAGED DIMENSIONS	230(H) x 140(W) x 540mm(D)