filter regulator LFR-3/8-D-5M-MIDI Part number: 162721 Classic

With metal bowl guard and pressure gauge, Degree of filtration 5 μm . With manual condensate drain.

Modern alternatives can be found by entering the first four characters of the type code in the search field.





FESTO

Data sheet

Feature	Value
Size	Midi
Series	D
Actuator lock	Rotary knob with lock
Assembly position	Vertical +/- 5°
Grade of filtration	5 μm
Condensate drain	manual rotary
Design structure	Filter regulator with pressure gauge
Max. condensate volume	43 cm3
Bowl guard	Metal bowl guard
Pressure gauge	with pressure gauge
Operating pressure	1 16 bar
Pressure regulation range	0.5 12 bar
Max. pressure hysteresis	0.2 bar
Standard nominal flow rate	2,400 l/min
Maritime classification	see certificate
Operating medium	Compressed air to ISO 8573-1:2010 [-:9:-]
	Inert gases
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further
	operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Storage temperature	-10 60 °C
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [6:8:4]
	Inert gases
Medium temperature	-10 60 °C
Ambient temperature	-10 60 °C
Product weight	900 g
Mounting type	Optional
	Line installation
	with accessories
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 2	G3/8
Materials note	Conforms to RoHS
Material housing	Zinc die-casting
Material bowl	PC