

SACC-CI-M12MSK-4PE-L180 THR T - Contact carrier



1420819

<https://www.phoenixcontact.com/gb/products/1420819>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Power, 5-position, Pin, straight, M12, coding: K, PCB mounting, THR solder connection, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- For compact devices: transmit high power in a confined space
- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration, thanks to mechanical port screw connections with threaded fastening
- Additional gasket for the device when not plugged in

Commercial data

Item number	1420819
Packing unit	60 pc
Minimum order quantity	60 pc
Sales key	ABQAGQ
Product key	ABQAGQ
GTIN	4055626280653
Weight per piece (including packing)	5.28 g
Weight per piece (excluding packing)	3.768 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Power
Sensor type	Power
Number of positions	5
Connection profile	4+PE
No. of power contacts	4
Seal present	yes
Shielded	no
Coding	K
Thread type	M12

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
Nominal voltage U_N	690 V
Nominal current I_N	16 A

Connection data

Connection method	THR solder connection
-------------------	-----------------------

Interfaces

Signal type/category	Power
----------------------	-------

Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 4T

Connector

SACC-CI-M12MSK-4PE-L180 THR T - Contact carrier



1420819

<https://www.phoenixcontact.com/gb/products/1420819>

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Coding	K

Cable/line

Signal type/category	Power
----------------------	-------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
	IP67, when plugged in
Ambient temperature (operation)	-25 °C ... 105 °C
	-40 °C ... 105 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-111

Mounting

Mounting type	PCB mounting
---------------	--------------

Packaging specifications


Type of packaging	Tray
Delivery state	with assembly pad

1420819

<https://www.phoenixcontact.com/gb/products/1420819>

Drawings

Schematic diagram



Connector pin assignment of M12 plug, 5-pos., K-coded, pin side view

SACC-CI-M12MSK-4PE-L180 THR T - Contact carrier




1420819

<https://www.phoenixcontact.com/gb/products/1420819>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1420819>

<div> cULus Recognized Approval ID: E468743-20180113</div>				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	600 V	16 A	-	-

SACC-CI-M12MSK-4PE-L180 THR T - Contact carrier



1420819

<https://www.phoenixcontact.com/gb/products/1420819>

Classifications

ECLASS

ECLASS-13.0	27440110
-------------	----------

ETIM

ETIM 9.0	EC003557
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1420819

<https://www.phoenixcontact.com/gb/products/1420819>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk