Stapler LXT®

DST112

18V • 7 – 10 mm

For easy material installation

A handy cordless 18V LXT® stapler for quick and easy fixing of construction plastics and other materials. Suitable for fitting upholstery, roofing panels, vapour barriers, underlay and other construction materials.



LXT

Technical specifications

Voltage LXT	✓
Staple Crown Width	10 mm
Staple range	7 - 10 mm
Staple Wire Section	0,5 x 0,7 mm
Fastener Magazine Capacity	150
Nominal Battery Voltage	18 V
Sound Pressure Level (L_{pA})	76 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s²
Vibration Uncertainty (K Factor)	1,5 m/s²
Tool weight with battery	1,5 - 1,8 kg
Product Dimensions (L x W x H):	235 x 94 x 165 mm
Staple measures	10 x 7 - 10 mm
Product net weight	1,5 kg

User benefits

- Fast and effortless fastening of building plastics and materials.
- Contact actuation mode drives staples repetitively for quick operation
- The rubber coating on the handle ensures a firm working grip
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com

Related products

Other

User manual

Parts drawing